
Internal hinge pin for aluminium profile

MiniTecPRFPIV

- Supplied with fixing kit
- Material: anodised aluminium




Uses

- Doors
- Panels
- Sections of structures that need to move


Assembly

- Slide the pin to the required location in the slot of the upper support profile and tighten. Repeat for lower profile.
- Add the spacers
- Insert the other part of the pin into the central hole at the top of the door profile, repeat for bottom of door
- Assemble the door into the frame ensuring the two parts of each hinge are in the correct position. Tighten the 2 grubscrews on each hinge



Info.

- Max. load: 250N



Typical application



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Weight (kg)	Stock*	Price each 1 to 49
PRF-PIV	Hinge pin	0,02	✔	8,28 €

*Depending on availability - Dimensions in mm

Our other products


SBS_L

Chain link, Stainless steel


EKGS

Backlash free coupling Gerwah®, from 0.5 to 35Nm


SA_SAKH


Housing for linear bearing, Closed - light load


BLHT20

Right angled gearbox, from 0.66 to 1.77 Nm


RBNpl

Fixed castor with plate, Steel - rubber


RPPM

RPP type belt per metre, RPP8 Steel cored polyurethane


DBL821

Idler for slat top chain, Range 821


KH

Linear bearing, Light


MLY_SS

Stainless steel bow shackle with eye bolt,


T5_11

T type timing pulley, T5 aluminium


SDG_SS

Universal adjustable guide support


SUA4_L

Chain link, Steel

Complementary products


PRF4545

Standard aluminium profile, 45 x 45 mm


PRF_ART

Articulated bracket for use with aluminium profile, With clamping ha...