

### Assembly key

- Materials:  
Shaft: chromed steel  
Handle: black plastic



### DISCOUNTS

Qty	1+	5+	10+
Disc. List	-5%	-5%	On request

Part number	Type	SW	Weight (kg)	Stock*	Price each 1 to 4
PRF-TOOL-H4	Clef de montage	4	-	✓	13,47 €
PRF-TOOL-H5	Clef de montage	5	-	✓	13,82 €

\*Depending on availability - Dimensions in mm

## Our other products



VELprf  
Clip-on base for hook-and-loop strip, Polyamide



PLB  
Cylindrical spacer, Brass



RHTplss  
High Temperature Castor, up to 200kg



NAST  
Cam follower without axial guide, With interior ring



SVR20  
Screwjack with travelling nut, with moving nut




BOX-TOR-INCH  
Box set of Nitrile O-rings in inch NBR90Sh A, For fasteners and fitt...



DOMI50  
Domino 50 adjustable slide, Slide DOMILINE 50 with counter and handw...



BLHT20  
Right angled gearbox, from 0.66 to 1.77 Nm



NK80  
Drylin®N miniature guiding system, Width 80mm



UTKswcr  
Utilittrak® 3 wheels carriage, Steel roller carriage



SSG1  
Stainless steel spur gear, Stainless steel 304L



SEV  
Vertical stirrup toggle clamp, Vertical Latch Clamp - stainless steel

## Complementary products



PRF4545\_P  
Stripp Aluminium profile with extendable slot, 45 x 45 mm