

Standard aluminium profile

Stock

PRF1932 **MiniTec**

Section: 19x32 mm

- Profile for creating modular structures
- To be cut to length once supplied
- Material: anodised aluminium
- Covers are not sold individually, please contact us for details

Accessories


- Universal fastener PRF-FIX-UNI
- Right angle PRF19-E
- Standard fastener PRF-FIX-STD
- Screwed-in assemblies

Uses

- Light supports
- Handles
- Detector and switch supports
- Frames



Typical application



DISCOUNTS profile DISCOUNTS cover

Qty	1+	5+	10+	Qty	1+	50+	100+
Disc.	List	-5%	On request	Disc.	List	-5%	On request

Part number	lx (cm ²)	ly (cm ²)	Length (mm)	Weight (kg/m)	Stock*	Price each
Profile						
PRF1932-3	3,105	1,527	3000	0,987	✓	56,11 €
Cover						
PRF1932-C		End cover with pin			✓	0,98 €

*Depending on availability - Dimensions in mm

Our other products



MCLred

Reducing sleeve
female/female,
Cylindrical - stainless
steel



TOL

Swivel head, Long



HRV

V-rail guidance
Simple Select®
system, Rail with
carriage



BLHT40

Right angled gearbox,
from 4 to 10.30 Nm



SRG

Adjustable latch
clamp with strike
plate, Stroke from
77,3mm to 83mm



CHTRB

Single and dual
output gearboxes, Up
to 16,5 Nm



T5M T10M

T type timing belt per
metre, T5 Steel cored
polyurethane



WTM

Tightening washer -
DIN6340, Steel



BFM2

Flanged bronze nut,
Bronze - 2 threads



YG4

HEAVY DUTY spur
gear, Steel 35NCD6



PTA50ssEB

Articulated foot with
sheet metal base



PRF4545

Standard aluminium
profile, 45 x 45 mm

Complementary products



PRF_FIX_UNI

Universal fastener for
aluminium profile,
Universal



PRF19_E

Bracket for aluminium
profile, PRF19 to
PRF45



BAC105

Storage bin, 8mm



BAC105

Storage bin, 8mm