

- *Material: grey ABS plastic*
- ***Not sold individually, please contact us for details***


Advantages

Accessories for the neat installation and finishing of the ***PR45-GOU-3*** *cable cover.*
- Avoids the need for cutting angled joints
-Gives a professional finish






Cover PRF45-GOU-C



End cap PRF45-GOU-E



Angle PRF45-GOU-A

DISCOUNTS

Qty.	1+	50+	100+
Disc.	List	-5%	On request

Part number	Type	Price each 1 to 49
PRF45-GOU-C	Cover	1,75 €
PRF45-GOU-E	End cap	1,68 €
PRF45-GOU-A	Angle	3,57 €

Our other products



PTKFss

Fixable foot for the food industry, Stainless steel - 3-A standard



PRF_BR

Clamp for aluminium profile, Clamp for profile



V3RA

3-spoked handwheel without handle, Polyamide



DOG111

Motor-gearbox 12V and 24V DC, from 1.5 to 6 Nm



MRA

Quick link, Steel



BPL

Ball transfer unit light duty, Light



GCH

Linear ball slide Eco Range, economy range



ACLEPP

Right angled bracket for aluminium profile, 4 holes



BPHF

Ball transfer unit push fit, Heavy



SLB

Indexing plunger, steel class 5.8



CNA-CNG

Right angled mounting plate, Right angled mounting plate for clevis



CHML50

Worm and wheel gear reducer, up to 107 Nm - Integrated torque limiter

Complementary products



PRF4545

Standard aluminium profile, 45 x 45 mm