


- Levelling foot with solid base
- Non slip base
- Materials:
 - Base: stainless steel AISI 304
 - Threaded rod: stainless steel AISI 304 (nut not supplied)
 - Sole: NBR rubber (Shore hardness 70)

Advantages

- Articulated rod allows auto-alignment with the ground
- Sole material ensures flexibility and grip



stainless steel



DISCOUNTS

Qty	1+	6+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	ØM	A	B	ØD	A/F	G	H	H1	Max. load (N)	Stock*	Price each
										✓	1 to 5
PRS80-16-50	M16	36	50	80	13	19,5	86	89	30000	✓	79,02 €
PRS80-16-75	M16	36	75	80	13	19,5	111	114	30000	-	79,87 €
PRS80-16-100	M16	36	100	80	13	19,5	136	139	30000	✓	80,82 €
PRS80-16-125	M16	36	125	80	13	19,5	159	164	30000	-	81,65 €
PRS80-16-150	M16	36	150	80	13	19,5	186	189	30000	-	82,61 €
PRS80-16-175	M16	36	175	80	13	19,5	211	214	30000	✓	83,46 €
PRS80-16-200	M16	36	200	80	13	19,5	236	239	30000	✓	84,42 €
PRS80-20-75	M20	36	75	80	13	19,5	111	114	30000	-	81,27 €
PRS80-20-100	M20	36	100	80	13	19,5	136	139	30000	-	82,16 €
PRS80-20-125	M20	36	125	80	13	19,5	161	164	30000	-	83,04 €
PRS80-20-150	M20	36	150	80	13	19,5	186	189	30000	-	83,95 €
PRS80-20-175	M20	36	175	80	13	19,5	211	214	30000	✓	84,83 €
PRS80-20-200	M20	36	200	80	13	19,5	236	239	30000	-	85,76 €
PRS80-20-225	M20	36	225	80	13	19,5	261	264	30000	-	86,65 €

*Depending on availability - Dimensions in mm

Our other products



Male rod ends ,
Stainless steel / PTFE



Chain sprocket -
Stainless steel, 9.525
(DIN 06B-1)



Double universal joint
- Stainless steel, Low
duty



Storage bin, 8mm




Arm with rotating
handle, Square bore



Spur gear - precision
range, Stainless steel
303



Square tube
connector, Fixed
angle



Worm and wheel gear
reducer, up to 41 Nm



High rigidity linear
slide, Rail - from 9320
N to 71300 N



Horizontal hook
toggle clamp,
Horizontal Hook



Manual workbench
press, Force up to
400kg



Guide for aluminium
profile, Rail for 8mm
wide slots

Complementary products



Articulated foot Ø83,
Ø 83