Module 2.0

Spur gear

S/Steel 303
S/Steel 316





- ***Quality grade 7e25 DIN 3961 (AGMA Q10)***
- *Material :*
  Stainless steel 303
  Stainless steel 316
- *Teeth profile conform to DIN 867*
- *Tooth thickness conforms to DIN 3967*
- *Efficiency approx 98%*

Options

- *Alternative bores (H7)*
- *Keyway conforming to DIN 6885 (JS9)*
- *Tapped hole*
- *Hole for dowel pin*

Info.

- *Torque figures are for 100 rpm and are given as a guide only*

Quality grade 7e25

DISCOUNTS


Qty	1+	6+	19+	50+
Disc.	List	-5%	-10%	On request

Part number S/steel303	Part number S/steel 316	Z Teeth	ØP Pitch	ØD External	ØA Bore	ØM Boss	Backlash (mm)	Torque (Nm) S/steel 303	Torque (Nm) S/steel316	Weight (kg)	Price each 1 to 5 S/steel303	Price each 1 to 5 S/steel 316
PSG2.0-18S	PSG2.0-18SL	18	36	40	10	30	0,129 - 0,051	7,37	5,73	0,249	83,28 €	95,60 €
PSG2.0-19S	PSG2.0-19SL	19	38	42	10	30	0,129 - 0,051	7,78	6,05	0,267	85,15 €	97,81 €
PSG2.0-20S	PSG2.0-20SL	20	40	44	10	30	0,129 - 0,051	10,35	8,05	0,287	86,96 €	99,81 €
PSG2.0-21S	PSG2.0-21SL	21	42	46	12	35	0,129 - 0,051	10,87	8,46	0,337	89,26 €	102,48 €
PSG2.0-22S	PSG2.0-22SL	22	44	48	12	35	0,129 - 0,051	11,39	8,86	0,358	90,60 €	104,06 €
PSG2.0-23S	PSG2.0-23SL	23	46	50	12	35	0,129 - 0,051	11,91	9,26	0,380	92,54 €	106,24 €
PSG2.0-24S	PSG2.0-24SL	24	48	52	12	35	0,129 - 0,051	12,43	9,66	0,404	94,58 €	108,57 €
PSG2.0-25S	PSG2.0-25SL	25	50	54	12	35	0,129 - 0,051	12,94	10,07	0,428	99,84 €	114,62 €
PSG2.0-26S	PSG2.0-26SL	26	52	56	12	35	0,171 - 0,069	15,84	12,32	0454	103,03 €	118,31 €
PSG2.0-27S	PSG2.0-27SL	27	54	58	12	35	0,171 - 0,069	16,44	12,79	0,480	106,67 €	122,51 €
PSG2.0-28S	PSG2.0-28SL	28	56	60	12	35	0,171 - 0,069	17,05	13,26	0,507	108,99 €	125,16 €

Dimensions in mm

Module 2.0





DISCOUNTS

Qty	1+	6+	19+	50+
Disc.	List	-5%	-10%	On request

Part number S/steel303	Part number S/steel 316	Z Teeth	ØP Pitch	ØD External	ØA Bore	ØM Boss	Backlash (mm)	Torque (Nm) S/steel 303	Torque (Nm) S/steel316	Weight (kg)	Price each 1 to 5 S/steel303	Price each 1 to 5 S/steel 316
PSG2.0-29S	PSG2.0-29SL	29	58	62	14	45	0,171 - 0,069	17,66	13,74	0,623	111,76 €	128,29 €
PSG2.0-30S	PSG2.0-30SL	30	60	64	14	45	0,171 - 0,069	20,10	15,63	0,653	114,20 €	131,12 €
PSG2.0-32S	PSG2.0-32SL	32	64	68	14	45	0,171 - 0,069	21,44	16,68	0,714	124,05 €	142,43 €
PSG2.0-35S	PSG2.0-35SL	35	70	74	14	45	0,171 - 0,069	23,45	18,24	0,815	136,89 €	157,20 €
PSG2.0-38S	PSG2.0-38SL	38	76	80	14	45	0,171 - 0,069	25,46	19,80	0,924	150,29 €	111,33 €
PSG2.0-40S	PSG2.0-40SL	40	80	84	16	55	0,171 - 0,069	34,24	26,63	1,113	156,64 €	179,82 €
PSG2.0-42S	PSG2.0-42SL	42	84	88	16	55	0,173 - 0,067	35,96	27,97	1,194	161,44 €	185,36 €
PSG2.0-45S	PSG2.0-45SL	45	90	94	16	55	0,173 - 0,067	38,52	29,96	1,325	168,42 €	193,36 €
PSG2.0-48S	PSG2.0-48SL	48	96	100	16	55	0,173 - 0,067	41,09	31,96	1,464	181,40 €	208,30 €
PSG2.0-50S	PSG2.0-50SL	50	100	104	20	65	0,173 - 0,067	50,76	39,48	1,677	194,21 €	222,95 €
PSG2.0-52S	PSG2.0-52SL	52	104	108	20	65	0,173 - 0,067	52,79	41,06	1,779	201,40 €	231,33 €
PSG2.0-55S	PSG2.0-55SL	55	110	114	20	65	0,173 - 0,067	55,83	43,42	1,940	227,43 €	261,18 €
PSG2.0-58S	PSG2.0-58SL	58	116	120	20	65	0,173 - 0,067	58,88	45,79	2,109	241,20 €	276,95 €
PSG2.0-60S	PSG2.0-60SL	60	120	124	20	65	0,173 - 0,067	72,48	56,37	2,227	247,34 €	284,01 €
PSG2.0-62S	PSG2.0-62SL	62	124	128	20	65	0,175 - 0,065	74,90	58,25	2,350	253,36 €	290,89 €


Dimensions in mm

Our other products



ATZYSS

Stainless steel diabolo shaped elasto mount, Stainless steel



STC

Shock Absorber - stop collar, Universal flange



SSE

Stainless steel spherical bearing, Stainless steel / PTFE



PW_PWG05

Worm - precision range, Stainless steel



WBGV

Lifting ring, Threaded



PRF1945

Standard aluminium profile, 19 x 45 mm



PT881

Drive sprocket for slat top chain, Range 881



PSG1S

Spur gear - precision range, Stainless steel 303



SEH

Horizontal stirrup toggle clamp,



SH0

Parallel axis helical gear, Steel 20NCD2



CQA30

Accessory for adjustment slide-



UGH20

H Type Guide units, For Ø20 actuators

Complementary products



PSG2

Spur gear - precision range, Pre-hardened Steel 35NCD6



PSG2S

Spur gear - precision range, Stainless steel 303