
Drive sprocket for plate chain

For chain ranges 821 and 805 — PT821

- ***For driving CAP821 and CAP805 plate chains***
- *With bore and keyway*
- *Materials:*
  Reinforced polyamide
  Stainless steel screws
- *Operating temp.: -10°C to +120°C*
- *For dimensions and bore tolerances, please refer to technical pages*




Advantage

- *Two part design facilitates easy assembly*

Easy assembly



Two part design



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request

Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PT821-25-30	25	153	153,2	30	0,9	70,12 €
PT821-25-35	25	153	153,2	35	0,9	70,12 €
PT821-25-40	25	153	153,2	40	0,9	70,12 €
PT821-25-45	25	153	153,2	45	0,9	70,12 €

Dimensions in mm

Our other products


RDS

Safety washer Hygienic Usit®, Stainless steel


VPPTss


Stainless steel handwheel with handle, Stainless steel 304


PCF2


Conical flexible mount, Oval base plate


PT820

Drive sprocket for slat top chain, Ranges 820 and 815


PRF_JL2

Lip seal for panel, Door seal - Ø 2mm


RPPM

RPP type belt per metre, RPP5 Steel cored polyurethane


METC


Flanged sintered bronze bush, Self-lubricating sintered bronze


DIA

Ring operated locking bolt, with ring


ACLLPP


Latch for aluminium profile, Spring


RPPM

RPP type belt per metre, RPP8 Steel


NPTR10

Adjustable cross clamp, Adjustable


B

Steel bevel gear, 1:1

Complementary products


CAP821

Slat top chain acetal, Large range 821


CAP805

Slat top chain stainless steel, Large range 805