Drive sprocket for plate chain

PT882 For chain range 882 TAB

- ***For driving CAP882T chains***
- *With bore and keyway*
- *Materials:*
  Reinforced polyamide
  Stainless steel screws
- *Operating temp.: -10°C to +120°C*
- *For dimensions and bore tolerances, please refer to technical pages*

Advantage


- *Two part design facilitates easy assembly*

Easy assembly





Two part design



DISCOUNTS

Qty.	1+	5+	10+
Disc.	List	-5%	On request


Part number	No. of teeth	ØDE	ØDP	Bore ØA	Weight (kg)	Price each 1 to 4
PT882-12-25	12	148,5	147,2	25	0,38	29,36 €
PT882-12-30	12	148,5	147,2	30	0,38	29,36 €
PT882-12-35	12	148,5	147,2	35	0,38	29,36 €
PT882-12-40	12	148,5	147,2	40	0,38	29,36 €
PT882-12-45	12	148,5	147,2	45	0,38	29,36 €

Dimensions in mm

Our other products



Sealing brush strip, 3m length



Lip seal for panel, Door seal - Ø 2mm



Drylin® W rail, Rail



Multifunction display, Mounting bracket for front mounting



Worm, Unhardened steel



Lifting sling, 2 eyelinks



Spur gear coaxial gearbox, from 20 to 68 Nm - Inline



Stainless steel rigging screw (hook/eye), Stainless steel



Steel spur gear, Steel 20NCD2



Panamech, Multi-Beam, Aluminium - with set screw



Universal latch key, Universal latch key



Right angled mounting plate, Right angled mounting plate for ball jo...

Complementary products