

# Articulated levelling foot, pressed base Ø100 **Ste** **Sta**

## PTA100 PTA100ss

Accepts loads up to 15.000N

- Articulated foot
- Up to +/- 10° from vertical
- Materials:


### Steel version:

Base: Galvanised sheet steel C40  
Shaft: Galvanised steel (nut not supplied)  
Sole: Vulcanised NBR rubber, hardness 80° Shore

### Stainless steel version:

Base: Stainless steel sheet 304  
Shaft: Stainless steel plate 304 (nut not supplied)  
Sole: Vulcanised NBR rubber, hardness 80° Shore

*Stainless steel version, sanded finish*



### Advantages

- Excellent Quality/Price ratio

### DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	Thread ØF	B	A	A/F	G	H	Load static (N)	Stock*	Price each 1 to 14
<b>Steel foot</b>										
PTA100-16-100	100	M16	100	38,0	16	28	137,5	15000	✓	25,53 €
PTA100-16-150	100	M16	150	38,0	16	28	187,5	15000	✓	28,05 €
PTA100-16-200	100	M16	200	38,0	16	28	237,5	15000	✓	28,98 €
PTA100-20-100	100	M20	100	39,0	20	28	138,5	15000	✓	26,76 €
PTA100-20-150	100	M20	150	39,0	20	28	188,5	15000	✓	29,72 €
PTA100-20-200	100	M20	200	39,0	20	28	238,5	15000	-	32,67 €
PTA100-24-100	100	M24	100	39,0	24	28	138,5	15000	-	31,63 €
PTA100-24-150	100	M24	150	39,0	24	28	188,5	15000	-	34,69 €
<b>Stainless steel foot</b>										
PTA100-16-100/SS	100	M16	100	39,5	13	30	139,5	15000	✓	49,66 €
PTA100-16-150/SS	100	M16	150	39,5	13	30	189,5	15000	✓	51,42 €
PTA100-16-200/SS	100	M16	200	39,5	13	30	239,5	15000	-	55,56 €
PTA100-20-100/SS	100	M20	100	43,0	17	30	143,0	15000	-	53,21 €
PTA100-20-150/SS	100	M20	150	43,0	17	30	193,0	15000	✓	56,75 €
PTA100-20-200/SS	100	M20	200	43,0	17	30	243,0	15000	-	60,88 €
PTA100-24-100/SS	100	M24	100	44,0	20	30	144,0	15000	-	57,33 €
PTA100-24-150/SS	100	M24	150	44,0	20	30	194,0	15000	-	59,12 €

\*Depending on availability - Dimensions in mm

## Our other products



BLHT30  
Right angled gearbox,  
from 1.65 to 4.40 Nm



SSG1\_304L  
Stainless steel spur  
gear, Stainless steel  
304L



STC  
Shock Absorber - stop  
collar, Universal  
flange



SSBRA  
Stainless steel bevel  
gear, 1:1



FIRSDC1Q60  
Speed controller 10A,  
10 A



PM3  
Worm and wheel set,  
Non hardened steel



GTC  
Belt tensioner, For  
standard applications



KB\_OP  
Open precision linear  
bearing, Precision -  
steel



OP3  
Mechanical digital  
position indicator, 4



HTD5M\_09  
HTD Heavy duty  
timing pulley, HTD5



SH2  
Parallel axis helical  
gear, Steel 20NCD2



T5P\_T10P  
Connecting plate for T  
type timing belts, T10

## Complementary products



PTA150  
Articulated levelling  
foot, pressed base  
Ø150, Ø 150