Articulated foot with sheet metal base Ø40

Max load: 4000N
Rubber sole in EPDM, blue

PTA40SS/EB

- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special sole for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load (N)	Stock*	Price per unit 1 to 5
PTA40-8-25/SS/EB	40	M8	25	26	6	15	51	3000	-	13,14 €
PTA40-8-50/SS/EB	40	M8	50	26	6	15	76	3000	-	13,53 €
PTA40-8-75/SS/EB	40	M8	75	26	6	15	101	3000	-	14,01 €
PTA40-10-25/SS/EB	40	M10	25	26	8	15	51	3000	-	14,31 €
PTA40-10-50/SS/EB	40	M10	50	26	8	15	76	3000	-	14,76 €
PTA40-10-75/SS/EB	40	M10	75	26	8	15	101	3000	-	15,21 €
PTA40-10-100/SS/EB	40	M10	100	26	8	15	126	3000	-	16,08 €
PTA40-10-125/SS/EB	40	M10	125	26	8	15	151	3000	-	16,71 €

** Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 cial2@hpceurope.com

Articulated foot with sheet metal base Ø50 Inx

PTA50SS/EB

Max load: 4000N
Rubber sole in EPDM, blue

- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part N°	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA50-10-75/SS/EB	50	M10	75	29	14	19	104	4,000	18,61 €
PTA50-10-125/SS/EB	50	M10	125	29	14	19	154	4,000	21,00 €
PTA50-12-75/SS/EB	50	M12	75	29	14	19	104	4,000	18,61 €
PTA50-12-125/SS/EB	50	M12	125	29	14	19	154	4,000	21,00 €
PTA50-16-75/SS/EB	50	M16	75	34	13	19	109	4,000	21,58 €
PTA50-16-100/SS/EB	50	M16	100	34	13	19	134	4,000	22,40 €
PTA50-16-150/SS/EB	50	M16	150	34	13	19	184	4,000	24,51 €

** Depending on availability - Dimensions in mm*

Articulated foot with sheet metal base Ø80

Max load: 10,000N
Rubber sole in EPDM, blue

PTA80SS/EB

- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special sole for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part N°	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA80-12-100/SS/EB	80	M12	100	35	14	25	135	10000	31,38 €
PTA80-12-150/SS/EB	80	M12	150	35	14	25	185	10000	33,65 €
PTA80-16-100/SS/EB	80	M16	100	35	13	25	135	10000	33,65 €
PTA80-16-150/SS/EB	80	M16	150	35	13	25	185	10000	35,85 €
PTA80-20-100/SS/EB	80	M20	100	38	17	25	138	10000	37,57 €
PTA80-20-150/SS/EB	80	M20	150	38	17	25	188	10000	40,32 €
PTA80-20-200/SS/EB	80	M20	200	38	17	25	238	10000	44,54 €

** Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 cial2@hpceurope.com

Articulated foot with sheet metal base Ø100

PTA100SS/EB

Max load: 15,000N
Rubber sole in EPDM, blue

- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue


Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment





DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part N°	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA100-16-100/SS/EB	100	M16	100	39.5	13	30	139.5	15000	48,36 €
PTA100-16-150/SS/EB	100	M16	150	39.5	13	30	189.5	15000	50,09 €
PTA100-16-200/SS/EB	100	M16	200	39.5	13	30	239.5	15000	54,00 €
PTA100-20-100/SS/EB	100	M20	100	43.0	17	30	143.0	15000	51,73 €
PTA100-20-150/SS/EB	100	M20	150	43.0	17	30	193.0	15000	55,07 €
PTA100-20-200/SS/EB	100	M20	200	43.0	17	30	243.0	15000	59,00 €
PTA100-24-100/SS/EB	100	M24	100	44.0	20	30	144.0	15000	55,66 €
PTA100-24-150/SS/EB	100	M24	150	44.0	20	30	194.0	15000	57,35 €

** Depending on availability - Dimensions in mm*

Articulated foot with sheet metal base Ø80

Max load: 10,000N
Rubber sole in EPDM, blue

PAMF80EB


- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue


Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special sole for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*





DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part N°	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PAMF80-12-100/EB	80	M12	100	35	14	25	135	10000	38,93 €
PAMF80-12-150/EB	80	M12	150	35	14	25	185	10000	41,14 €
PAMF80-16-75/EB	80	M16	75	35	13	25	110	10000	39,46 €
PAMF80-16-125/EB	80	M16	125	35	13	25	160	10000	42,27 €
PAMF80-16-175/EB	80	M16	175	35	13	25	210	10000	45,06 €
PAMF80-20-100/EB	80	M20	100	38	17	25	138	10000	45,06 €
PAMF80-20-150/EB	80	M20	150	38	17	25	188	10000	47,85 €
PAMF80-20-200/EB	80	M20	200	38	17	25	238	10000	52,03 €


**Within the limits of available stock - Dimensions in mm*

Articulated foot with sheet metal base Ø100

PAMF100EB

Max load: 15,000N
Rubber sole in EPDM, blue

- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special pad for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part N°	Threading ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PAMF100-16-100/EB	100	M16	100	39.5	13	30	139.5	15000	56,53 €
PAMF100-16-150/EB	100	M16	150	39.5	13	30	189.5	15000	58,24 €
PAMF100-16-200/EB	100	M16	200	39.5	13	30	239.5	15000	62,18 €
PAMF100-20-100/EB	100	M20	100	43.0	17	30	143.0	15000	59,90 €
PAMF100-20-150/EB	100	M20	150	43.0	17	30	193.0	15000	63,32 €
PAMF100-20-200/EB	100	M20	200	43.0	17	30	243.0	15000	67,23 €

** Depending on availability - Dimensions in mm*

Tel. +33(0)4 37 496 496 cial2@hpceurope.com

Our other products




VLBS

Folding lifting ring for welding, Folding - for welding



PPOss

Pad eye on mounting plate oval, Stainless steel



M2

Wormwheel, Machined plastic (delrin)



RAGFLOW

Floway2® roller track, Roller track



BOX-SHNA

Hexagonal nut - DIN934, Box set of steel nuts



M1

Worm, Machined plastic (delrin)



EPRF

High helix leadscrew, Flanged nut - up to 40mm per rotation



CHALss

Piano hinge, Stainless steel



UTKswcr

Utilitrak® 3 wheels carriage, Steel roller



BLHM70

Right angled gearbox, up to 128 Nm



DOMI80

Domino 80 adjustable slide, Slide DOMILINE



ACM_DZ

Clip for bonnet fastener, Clip

Complementary products



PTA50ssEB

Articulated foot with sheet metal base Ø50, 4 000N



PTA80ssEB

Articulated foot with sheet metal base Ø80, 10000N



PTA100ssEB

Articulated foot with sheet metal base Ø100, 15000N



PAMF80EB

Articulated foot with sheet metal base Ø80, Articulated foot