

Stack Threaded eye hook stainless steel

Diameter M6 to M12


PTBss

Eye bolt

- Material : Stainless steel 316
- Product carries no certification marking

Utilisation

The breaking strength is obtained by multiplying the SWL by a factor of safety of 4



INCREASED STOCK

DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØM	L	ØA	ØB	CMU (kg)	Weight (kg)	Stock*	Price each 1 to 19
PTB6-40/SS	M6	40	12	22	120	0,020	✓	5,03 €
PTB6-60/SS	M6	60	12	22	120	0,030	✓	5,39 €
PTB6-80/SS	M6	80	12	22	120	0,030	✓	5,79 €
PTB8-60/SS	M8	60	14	26	225	0,050	✓	7,03 €
PTB8-80/SS	M8	80	14	26	225	0,055	-	7,70 €
PTB8-100/SS	M8	100	14	26	225	0,060	✓	8,52 €
PTB10-100/SS	M10	100	16	30	375	0,105	✓	13,16 €
PTB12-120/SS	M12	120	16	35	600	0,165	✓	20,71 €

Dimensions in mm

Our other products



LPCM
Lever with cylindrical handle, Black Duroplast, steel lever



IN1
Internal gear, Steel 20NCD2



UGH25
H Type Guide units, For Ø25 actuators



CHTRB
Single and dual output gearboxes, Up to 4,7 Nm



DCG
Suction cup, 2.5 bellows, silicon




G-ECO
Eco range Spur gear, Steel C45



BLHB20
Right angled gearbox, bored shafts, up to 1.77 Nm



G3-ECO
Eco range Spur gear, Steel C45



BG
Oldham coupling, With set screw



NIN
Self-locking nut, A2 Stainless steel



YG1
HEAVY DUTY spur gear, Steel 35NCD6



PRF_GAL
Roller for aluminium profile, Fixing kit for roller concentric


Complementary products




TAC_SS
Stainless steel rigging screw (hook/eye), Stainless steel



TCC
Rigging screw (hook/hook), Steel



CAB
Stainless steel cable, Stainless steel



CAB
Galvanised steel cable, Galvanised steel