

# Sta Stock Threaded eye hook stainless steel

Diameter M6 to M12


PTBss

## Eye bolt

- Material : Stainless steel 316
- Product carries no certification marking

## Utilisation

The breaking strength is obtained by multiplying the SWL by a factor of safety of 4



**INCREASED STOCK**

## DISCOUNTS

Qty	1+	20+	40+	60+	80+	100+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number	ØM	L	ØA	ØB	CMU (kg)	Weight (kg)	Stock*	Price each 1 to 19
PTB6-40/SS	M6	40	12	22	120	0,020	✓	5,03 €
PTB6-60/SS	M6	60	12	22	120	0,030	✓	5,39 €
PTB6-80/SS	M6	80	12	22	120	0,030	✓	5,79 €
PTB8-60/SS	M8	60	14	26	225	0,050	✓	7,03 €
PTB8-80/SS	M8	80	14	26	225	0,055	-	7,70 €
PTB8-100/SS	M8	100	14	26	225	0,060	✓	8,52 €
PTB10-100/SS	M10	100	16	30	375	0,105	✓	13,16 €
PTB12-120/SS	M12	120	16	35	600	0,165	✓	20,71 €

Dimensions in mm

## Our other products




PRF\_JL2  
Lip seal for panel,  
Door seal - Ø 2mm



WING  
Manually tightened  
wing nut, Steel (ANSI  
B18-17)



B52  
Panamech, Multi-  
Beam, Aluminium -  
with set screw



CRM  
Moulded nylon rack,  
Nylon



GBS  
Nut for ballscrew,  
Flanged ballscrew nut



VDSCB  
Sliding lock  
adjustment system,  
Blocking wedge for  
sliding lock for ...



PSPT  
Flexible tube handle,  
PVC



RPCpl  
Swivel castor with  
plate, Steel -  
Polyamide



BHEX  
Hexagonal cap, Black  
technopolymer



PITA  
Locking bolt, with T  
handle



DP  
Dowel pin, Solid ISO  
2338



G2  
Steel spur gear, Steel  
20NCD2


## Complementary products




TAC\_SS  
Stainless steel rigging  
screw (hook/eye),  
Stainless steel



TCC  
Rigging screw  
(hook/hook), Steel



CAB  
Stainless steel cable,  
Stainless steel



CAB  
Galvanised steel  
cable, Galvanised  
steel