
Adjustable suction-cup support

Increased grip


PV2R

- **Allows vacuum suction cups to be integrated into a handling system**
- Materials :
  Aluminium
  Screws : steel



Advantages

- Infinitely variable angle of adjustment
- No circlips required





Exploded view

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØA	B	ØC	ØD	L	⍁F	N	P	Weight (g)	Price each 1 to 9
PV20-1/4-50/2R	20	19	G1/4"	G1/4"	50	24	12	16,5	57	70,81 €
PV20-1/4-100/2R	20	19	G1/4"	G1/4"	100	24	12	16,5	71	73,65 €
PV20-1/4-150/2R	20	19	G1/4"	G1/4"	150	24	12	16,5	86	77,92 €

Dimensions in mm

Our other products



T5-10ECO

T type timing pulley, Economy range - T5 aluminium



NCT_AT

Variable angle connector, Variable angle



ADL_M

Male eye bolt conforms to DIN580, Steel



SSB

Stainless steel bevel gear, 1:1



PCLA_M

Technopolymer clamping lever - female, Plastic



WJUM20

Drylin® W bearing block, Slide



DOMI30

Domino 30 adjustable slide, Slide DOMILINE 30 with counter and handw...




BCM_T

Driving collar, Driving collar



BH01

Single housed bearing, Bearing fitted with adhesive



PF30NM

Worm and wheel gear reducer, up to 8.8 Nm



LRR

Spring loaded latch, Spring loaded latch



CHINV

Invisible hinge, Invisible - Opening up to 90°

Complementary products