

Small lobed handle


PVL

With square bore

- ***Handling element***
- *Max working temperature: 100°C*
- *Material:*
  Polyamide
- *Not sold individually,*
  please contact-us for details







DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc	Net	-5%	-10%	-15%	-20%	On request

Part N°	ØA	ØB	C	T	F	G	Weight (g)	Stock*	Price each 1 to 9
PVL40-6/SQ	40	20	9	6x6	1	8	10	✔	2,35 €
PVL40-8/SQ	40	20	9	8x8	1	8	10	✔	2,35 €

All dimensions in mm

Our other products



SDB

Locking bolt support bracket, Mounting holes at 90° to locating bolt



AT5-BAR

AT type tooth bar stock, AT5



VAP

Magnetic stud with central hole, With central hole



ZG3

Plastic spur gear, Machined plastic (delrin)



CHA1056-UPA

Molded polyamide face-mounted hinge, Black polyamide



T2

T type timing belt, T2.5 Steel cored polyurethane



G-ECO25

Eco range Spur gear, Steel C45



PITA

Locking bolt, with T handle



PHTss

Pull handle, Up to 250 °C



SHA

Handwheel without handle, Polyamide



BOXdhx

Boxed set of threaded dowel pins DIN7979D,



PSP

Support profile, Panel support

Complementary products



BMF

Knurled knob - female, Knurled - blind



GLB

Small 6 lobe threaded handle - female, Technopolymer - Brass



GGB

Female wing knob, Fully threaded