Manual bevel gearbox

RAM30

Manual torque up to 4 Nm

- ***Manually operated bevel gearbox***
- *Ratios from 1:1*
- *Materials:*
  Housing: Glass fibre reinforced PA6
  Bevel gears: Case hardened steel





Info


- *Not suitable for motorised applications*

Accessories


- ***MBEX** handle* **(tome 2 p.249)**
- ***AHEX** hexagonal shaft* **(tome 2 p.248)**







For manual operation only



DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-15%	On request

Part number	Ratio	Input	Output	Max torque (Nm)	Stock*	Price each 1 to 9
RAM30-1	1:1	hex 6mm	hex 6mm	4	✔	65,57 €


**Depending of availability - Dimensions in mm*

Manual bevel gearbox

Manual torque up to 6 Nm

RAM35

- ***Manually operated bevel gearbox***
- *Ratios from 1:1 to 2:1*
- *Materials:*
  Housing: Glass fibre reinforced PA6
  Bevel gears: Case hardened steel





Info


- *Not suitable for motorised applications*


Accessories

- **MBEX** *handle* **(tome 2 p.249)**
- **AHEX** *hexagonal shaft* **(tome 2 p.248)**









For manual operation only

DISCOUNTS

Qty	1+	10+	25+	50+
Disc.	List	-5%	-15%	On request

Part number	Ratio	Input	Output	Max torque (Nm)	Stock*	Price each 1 to 9
RAM35-1	1:1	hex 7mm	hex 7mm	6	✔	74,64 €
RAM35-2	2:1	hex 7mm	hex 7mm	6	✔	62,09 €

**Depending of availability - Dimensions in mm*