

Grey rubber wheel

RBG

For medium loads up to 120kg

- **Light industrial wheel with a semi-elastic solid rubber tyre**

- **Material:**

85° Shore vulcanised grey rubber tyre

Polypropylene rim

- **Smooth central bore**

- **Working temperature range - 20°C to + 60°C**

Advantages

- **Soft and silent**

- **Absorbs shock and vibration**

- **Will not damage floors**



Noise absorbing



ØD



B



C



ØA

DISCOUNTS

| | | | |
|-------|------|-----|------------|
| Qty | 1+ | 10+ | 30+ |
| Disc. | List | -5% | On request |

| Part number | ØD | B | C | ØA | Maximum load (kg) | Stock* | Price each 1 to 9 |
|--------------|-----|----|----|----|-------------------|--------|-------------------|
| RBG50-22/ML | 50 | 22 | 28 | 8 | 40 | ✓ | 1,50 € |
| RBG60-24/ML | 60 | 24 | 28 | 8 | 50 | ✓ | 1,92 € |
| RBG80-23/ML | 80 | 23 | 28 | 8 | 65 | ✓ | 3,02 € |
| RBG100-26/ML | 100 | 26 | 28 | 8 | 75 | ✓ | 3,60 € |
| RBG100-32/ML | 100 | 32 | 34 | 10 | 100 | - | 4,35 € |
| RBG125-32/ML | 125 | 32 | 34 | 10 | 120 | 4 | 5,63 € |

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



CCL
Standard wire
thimble, Steel



TBbutee
Axial thrust bearing,
Steel balls



NTM
Nylon tipped set
screw, Nylon-point



RCX-6
Spherical tilt washer -
DIN6319, concave



H0
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



TBD
Manual leadscrew
table with opposing
threads, 40kg



SVR15
Screwjack with
travelling nut, with
moving nut



PTGP
Tensioner pulley, For
flat belts



NCT
Square tube
connector, Fixed
angle



ZG0
Plastic spur gear,
Machined plastic
(delrin)



CHMR30
Worm and wheel gear
reducer, up to 28 Nm



AT10courroie
AT type timing belt,
AT10 Steel cored
polyurethane

Complementary products



RBGtc
Swivel castor with
central hole, Steel -
grey rubber - with
double b...



RBGpl
Fixed castor with
plate, Steel - grey
rubber



RBGtc
Swivel castor with
central hole, Steel -
grey rubber



RBGpl
Swivel castor with
plate, Steel - grey
rubber