

Castor with central hole

RBGTC For medium loads up to 110kg

- **Light industrial swivel castor with central hole**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
 - Top plate: pressed steel sheet, protected by bright zinc plating
 - Grey vulcanized rubber wheel 85°Shore (see RBG)
 - Smooth central bore
- Working temperature range: - 20°C to + 60°C

Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors

Swivel



ØD



B



H



ØE



ØK


DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
Swivel								
RBG50/TC/P	50	22	76	10	98	45	✓	3,91 €
RBG60/TC/P	60	24	85	10	110	55	✓	4,44 €
RBG80/TC/P	80	23	105	10	138	65	✓	5,71 €
RBG100/TC/P	100	26	121	10	166	75	✓	6,97 €
RBG125/TC/P	125	32	158	13	216	110	✓	10,68 €
Swivel with double lock								
RBG50/TC/PDB	50	22	76	10	172	45	4	5,79 €
RBG60/TC/PDB	60	24	85	10	172	55	4	6,00 €
RBG80/TC/PDB	80	23	105	10	188	65	✓	7,19 €
RBG100/TC/PDB	100	26	121	10	188	75	✓	10,20 €
RBG125/TC/PDB	125	32	158	13	220	110	✓	14,95 €

Dimensions in mm

Our other products



TC1rp
Automatic chain tensioner, With 180° guide



PRF-P
Aluminium profile feet support, For feet or casters



SCR
Suction cup threaded insert, Insert for suction cup - Socket screw



TFR
Rigid manual tensioner, Fixed



TOL
Swivel head, Long



BTCW
Cap for square tube to be welded, To be welded



HCA
Magnetic screw with socket, Steel



BSPM
Miniature ballscrew, Nut+rolled ballscrew



PLB
Cylindrical spacer, Brass



GLT3E-58
Telescopic drawer,



PDM_PDV
Detectable plastic palm grip, blue thermoplastic



ESCON
Speed controller 5A accessories, Kit of 4 cables for DC motor

Complementary products



RBG
Wheel, Grey rubber - Polypropylene rim



RPCtc
Swivel castor with central hole, Steel - Polyamide



RBNtc
Swivel castor with central hole, Steel - rubber



RPCtssc
Swivel castor with central hole, Stainless steel - Polyamide - with ...