

Black rubber covered wheel

For heavy loads up to 215kg

RBN

- Industrial castor with a semi-elastic solid rubber tyre
- Material:
 - 85° Shore vulcanised black rubber tyre
 - Polypropylene rim
- Smooth central bore
- Working temperature range: - 20°C to + 60°C

Advantages

- Soft and silent
- Absorbs shock and vibration
- Will not damage floors

Noise absorbing



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RBN80-34/ML	80	34	40	12	75	✓	2,79 €
RBN100-35/ML	100	35	39	12	100	✓	3,31 €
RBN125-38/ML	125	38	45	15	125	✓	5,19 €
RBN150-40/ML	150	40	45	15	150	✓	7,36 €
RBN160-38/ML	160	38	60	20	150	-	7,67 €
RBN200-47/ML	200	47	60	20	215	-	11,04 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019


273

Our other products



SVG

Adjustable latch clamp with strike plate, Stroke from 82mm to 92mm



KITdog

24V DC motorisation kit, Worm and wheel



METC

Flanged sintered bronze bush, Self-lubricating sintered bronze



VDSQ

Sliding lock adjustment system, Sliding lock for square profile



ACLRP

Wheel for aluminium profile, Integrated bearing



PRF_PL_4590

Joining plate for aluminium profile, Joint plate - 45x90 mm



HFL

One way needle bearing, Needle bearing



VRC1

Retaining clamp, single sided, Single sided



GCB880

Curved track for slat top chain, Ranges 880



V3RA_PT

3-spoked handwheel with handle,



NDS20

Double cross clamp, Parallel



HG5

Steel spur gear, Steel 20NCD2

Complementary products



RBNtc

Swivel castor with central hole, Steel - rubber



RBNtc

Swivel castor with central hole, Steel - rubber - with double brake



RBNpl

Fixed castor with plate, Steel - rubber



RBNpl

Swivel castor with plate, Steel - rubber