

Rubber castor with mounting plate

For heavy loads up to 215kg

RBNPL


- Industrial wheel suitable for loads up to 215kg
- Swivel system uses two sets of ball bearings
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
 - Baseplate: pressed steel sheet, protected by bright zinc plating
 - Black vulcanized rubber wheel, 85°Shore (see RBN)
- Smooth central bore
- Working temperature range: - 20°C to + 60°C

Swivels



Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max. load (kg)	Stock*	Price each 1 to 9
Fixed										
RBN80/PL/F	80	34	109	110x85	80x60	8	-	75	✓	7.38 €
RBN100/PL/F	100	35	126	110x85	80x60	8	-	100	✓	8.39 €
RBN125/PL/F	125	38	153	110x85	80x60	8	-	125	✓	11.15 €
RBN150/PL/F	150	40	180	110x85	80x60	8	-	150	✓	14.29 €
RBN160/PL/F	160	38	180	135x110	105x80	11	-	150	✓	19.59 €
RBN200/PL/F	200	47	241	135x110	105x80	11	-	215	-	25.73 €
Swivel										
RBN80/PL/P	80	34	109	110x85	80x60	8	158	75	✓	9.83 €
RBN100/PL/P	100	35	126	110x85	80x60	8	182	100	✓	10.85 €
RBN125/PL/P	125	38	153	110x85	80x60	8	210	125	✓	13.01 €
RBN150/PL/P	150	40	180	110x85	80x60	8	242	150	✓	15.89 €
RBN160/PL/P	160	38	180	135x110	105x80	11	267	150	-	22.97 €
RBN200/PL/P	200	47	241	135x110	105x80	11	320	215	-	30.80 €
Swivel with double lock										
RBN80/PL/PDB	80	34	109	110x85	80x60	8	290	75	✓	14.68 €
RBN100/PL/PDB	100	35	126	110x85	80x60	8	290	100	✓	15.71 €
RBN125/PL/PDB	125	38	153	110x85	80x60	8	290	125	✓	18.60 €
RBN150/PL/PDB	150	40	180	110x85	80x60	8	290	150	-	20.75 €
RBN160/PL/PDB	160	38	180	135x110	105x80	11	267	150	✓	26.85 €
RBN200/PL/PDB	200	47	241	135x110	105x80	11	320	215	-	38.51 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

275

Our other products



HK

Manual locking clamp,
Manual locking clamp
LWH



PW_PWG2

Worm - precision
range, Stainless steel



PSG085

Spur gear - precision
range, Stainless steel
303



PTA80

Articulated levelling
foot, pressed base
Ø80, Ø 80



PSG125S

Spur gear - precision
range, Stainless steel
303



PRES

Manual workbench
press accessory for
PRES-3HR end
PRES-4HR, Set of s...



LSAG

Precision linear rotary
ball spline, Rail - from
514 N to 15386 N




BOX-TOR-INCH

Box set of Nitrile O-
rings in inch NBR90Sh
A, For fasteners and
fitt...



BMM

Knurled knob - male,
Knurled



PRF_PIV

Internal hinge pin for
aluminium profile,
Internal hinge pin



CHMR90

Worm and wheel gear
reducer, up to 540
Nm



HLC19

Right angle spiro
bevel gearbox, Up to
43Nm

Complementary products



RPCplss

Swivel castor with
double brake,
Stainless steel -
Polyamide



RPCpl

Swivel castor with
double brake, Steel -
Polyamide



RBN

Wheel, Rubber tyre -
Polypropylene rim



RBNpl

Swivel castor with
plate, Steel - rubber