

# Rubber castor with mounting plate

For heavy loads up to 215kg

RBNPL


- Industrial wheel suitable for loads up to 215kg
- Swivel system uses two sets of ball bearings
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
  - Baseplate: pressed steel sheet, protected by bright zinc plating
  - Black vulcanized rubber wheel, 85°Shore (see RBN)
- Smooth central bore
- Working temperature range: - 20°C to + 60°C

Swivels



## Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors



## DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max. load (kg)	Stock*	Price each 1 to 9
<b>Fixed</b>										
RBN80/PL/F	80	34	109	110x85	80x60	8	-	75	✓	7.38 €
RBN100/PL/F	100	35	126	110x85	80x60	8	-	100	✓	8.39 €
RBN125/PL/F	125	38	153	110x85	80x60	8	-	125	✓	11.15 €
RBN150/PL/F	150	40	180	110x85	80x60	8	-	150	✓	14.29 €
RBN160/PL/F	160	38	180	135x110	105x80	11	-	150	✓	19.59 €
RBN200/PL/F	200	47	241	135x110	105x80	11	-	215	-	25.73 €
<b>Swivel</b>										
RBN80/PL/P	80	34	109	110x85	80x60	8	158	75	✓	9.83 €
RBN100/PL/P	100	35	126	110x85	80x60	8	182	100	✓	10.85 €
RBN125/PL/P	125	38	153	110x85	80x60	8	210	125	✓	13.01 €
RBN150/PL/P	150	40	180	110x85	80x60	8	242	150	✓	15.89 €
RBN160/PL/P	160	38	180	135x110	105x80	11	267	150	-	22.97 €
RBN200/PL/P	200	47	241	135x110	105x80	11	320	215	-	30.80 €
<b>Swivel with double lock</b>										
RBN80/PL/PDB	80	34	109	110x85	80x60	8	290	75	✓	14.68 €
RBN100/PL/PDB	100	35	126	110x85	80x60	8	290	100	✓	15.71 €
RBN125/PL/PDB	125	38	153	110x85	80x60	8	290	125	✓	18.60 €
RBN150/PL/PDB	150	40	180	110x85	80x60	8	290	150	-	20.75 €
RBN160/PL/PDB	160	38	180	135x110	105x80	11	267	150	✓	26.85 €
RBN200/PL/PDB	200	47	241	135x110	105x80	11	320	215	-	38.51 €

Dimensions in mm

**0 825 88 6000**  
Service 0,15 € / min  
+ prix appel

cial2@hpceurope.com

**HPC**

SUPPLEMENT 2019

275

## Our other products



MDB\_MTB  
Moulded plastic bevel gear (nylon), 3:1



PR821  
Idle sprocket for slat top chain, Ranges 821 and 805



GE32  
Sprung toggle latch with connecting link, Standard



AC156-157  
Strike for toggle latch, 25.5mm



BLHM60  
Right angled gearbox, double output shafts, up to 70 Nm



BLHM70  
Right angled gearbox, up to 128 Nm



DOG319  
Motor-gearbox 12V and 24V DC, from 4 to 9 Nm



CSSSS  
Stainless steel spherical bearing, Stainless steel / PTFE



HG5-ECO  
Eco range Spur gear, Steel C45



GE\_ET\_2RS  
Spherical bushing, Hard chromium / Teflon contact with



PM3  
Worm and wheel set, Machined plastic (delrin)



RFK28B  
Hypoid gearbox - Stainless steel, up to 130 Nm

## Complementary products



RPCpl  
Swivel castor with plate, Steel - Polyamide



RPCplss  
Swivel castor with plate, Stainless steel - Polyamide



RBN  
Wheel, Rubber tyre - Polypropylene rim



RBNpl  
Swivel castor with double brake, Steel - rubber