

Rubber castor with mounting plate

For heavy loads up to 215kg

RBNPL


- Industrial wheel suitable for loads up to 215kg
- Swivel system uses two sets of ball bearings
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
 - Baseplate: pressed steel sheet, protected by bright zinc plating
 - Black vulcanized rubber wheel, 85°Shore (see RBN)
- Smooth central bore
- Working temperature range: - 20°C to + 60°C

Swivels



Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max. load (kg)	Stock*	Price each 1 to 9
Fixed										
RBN80/PL/F	80	34	109	110x85	80x60	8	-	75	✓	7.38 €
RBN100/PL/F	100	35	126	110x85	80x60	8	-	100	✓	8.39 €
RBN125/PL/F	125	38	153	110x85	80x60	8	-	125	✓	11.15 €
RBN150/PL/F	150	40	180	110x85	80x60	8	-	150	✓	14.29 €
RBN160/PL/F	160	38	180	135x110	105x80	11	-	150	✓	19.59 €
RBN200/PL/F	200	47	241	135x110	105x80	11	-	215	-	25.73 €
Swivel										
RBN80/PL/P	80	34	109	110x85	80x60	8	158	75	✓	9.83 €
RBN100/PL/P	100	35	126	110x85	80x60	8	182	100	✓	10.85 €
RBN125/PL/P	125	38	153	110x85	80x60	8	210	125	✓	13.01 €
RBN150/PL/P	150	40	180	110x85	80x60	8	242	150	✓	15.89 €
RBN160/PL/P	160	38	180	135x110	105x80	11	267	150	-	22.97 €
RBN200/PL/P	200	47	241	135x110	105x80	11	320	215	-	30.80 €
Swivel with double lock										
RBN80/PL/PDB	80	34	109	110x85	80x60	8	290	75	✓	14.68 €
RBN100/PL/PDB	100	35	126	110x85	80x60	8	290	100	✓	15.71 €
RBN125/PL/PDB	125	38	153	110x85	80x60	8	290	125	✓	18.60 €
RBN150/PL/PDB	150	40	180	110x85	80x60	8	290	150	-	20.75 €
RBN160/PL/PDB	160	38	180	135x110	105x80	11	267	150	✓	26.85 €
RBN200/PL/PDB	200	47	241	135x110	105x80	11	320	215	-	38.51 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

275

Our other products



SEV
Vertical stirrup toggle clamp, Vertical Latch Clamp - steel



BGC
Oldham coupling, Clamp



NJM
Multiple junction clamp, Multiple



HRV
V-rail guidance Simple Select® system, Rail with carriage




LVT
Miniature motorised actuator 2A, 2 amperes



PO
Pull handle - Multi-selector, Tapped recessed insert



GLB
Small 6 lobe threaded handle - female, Technopolymer - Brass



KITbuh
24V DC motorisation kit, Planetary gears



BC2
Panamech, Multi-Beam, Aluminium - with clamping jaw



GP
Spring loaded toggle latch, Standard (GP22-GP23)



ACLBMC
Detector support for aluminium profile, Sensor holder



SH2
Parallel axis helical gear, Machined plastic (delrin)

Complementary products



RBN
Wheel, Rubber tyre - Polypropylene rim



RURp
Fixed castor with plate, Polyurethane - Aluminium rim (Free running)



RPCpl
Fixed castor with plate, Steel - Polyamide



RPCplss
Fixed castor with plate, Stainless steel - Polyamide