

# Rubber castor with central hole

## RBNTC

For heavy loads up to 215kg


- **Industrial wheel suitable for loads up to 215kg**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- **Materials:**
  - Baseplate: pressed steel sheet, protected by bright zinc plating
  - Black vulcanized rubber wheel 85°Shore (see RBN)
- Smooth central bore
- Working temperature range: - 20°C to + 60°C



Swivel with double locks

### Advantages

- Soft and silent
- Absorbs shock and vibration
- Will not damage floors



### DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Maximum load (kg)	Price each 1 to 9
<b>Swivel</b>							
RBN80/TC/P	80	34	105	12	158	75	9,76 €
RBN100/TC/P	100	35	125	12	182	100	10,76 €
RBN125/TC/P	125	38	152	12	210	125	13,31 €
RBN150/TC/P	150	40	179	12	242	150	17,17 €
RBN160/TC/P	160	38	188	12,5	267	150	24,29 €
RBN200/TC/P	200	47	232	12,5	320	215	29,54 €
<b>Swivel with double lock</b>							
RBN80/TC/PDB	80	34	105	12	290	75	14,96 €
RBN100/TC/PDB	100	35	125	12	290	100	15,80 €
RBN125/TC/PDB	125	38	152	12	290	125	18,40 €
RBN150/TC/PDB	150	40	179	12	290	150	23,29 €
RBN160/TC/PDB	160	38	188	12,5	267	150	36,40 €
RBN200/TC/PDB	200	47	232	12,5	320	215	42,12 €

Dimensions in mm

## Our other products



SHW  
Plain washer, A2  
Stainless steel



SHN  
Hexagonal nut  
DIN934, Steel (Class  
6[8])



ACLEFS  
Floor anchor for  
aluminium profile,  
Adjustable



RFVcap  
Stainless steel  
protective cover,  
Open protective cover



LC  
Friction clutch, 30 to  
240 Nm



AT5M AT10M  
AT type timing belt  
per metre, AT10 Steel  
cored polyurethane



BPHF  
Ball transfer unit push  
fit, Heavy



OP7  
Mechanical digital  
position indicator, 5  
numbers



GAL\_20  
Conveyor roller for  
Ø20mm spindle, Self-  
aligning



BPPE  
Ball transfer unit push  
fit, Light



BAC105  
Storage bin, 8mm



GAL\_25  
Ø25 conveyor roller,  
Without ball bearing

## Complementary products



RBN  
Wheel, Rubber tyre -  
Polypropylene rim



RBGtc  
Swivel castor with  
central hole, Steel -  
grey rubber



RBNtc  
Swivel castor with  
central hole, Steel -  
rubber - with double  
brake



RPCtc  
Swivel castor with  
central hole, Steel -  
Polyamide