

# Hypoid gearbox

Sta

## RFK38B

## Torque up to 200Nm

- Ideal gearbox for use in the food industry
- Ratios from 7.5:1 to 60:1
- 2-stage reduction
- B14 flange
- Rounded and polished surfaces to avoid material retention
- Lubricated using food quality grease
- 90% efficient
- Material:
  - 316 stainless steel housing





### Accessories

- Can be used with a DER 4-pole motor to create a motor-gearbox
- Torque arms, mounting bracket and protective cover

### Info

- All information is engraved directly on to gearbox rather than being on a tag plate to avoid accumulating dirt etc.



Output shaft

### Flange dimensions

	ØD	K	H	ØP	ØM	ØN	E	ØT
Flange 71B14	14	5	16,3	105	85	70	112,5	7
Flange 80B14	19	6	21,8	120	100	80	132,5	7
Flange 90B14	24	8	27,3	140	115	95	132,5	9

### DISCOUNTS

Qty	1+	2+	4+
Disc.	Net	-5%	On request

Part N°			Nominal reduction ratio	Actual reduction ratio	Price each
Flange 71B14	Flange 80B14	Flange 90B14			
	RFK38B-7.5-80B14/SS	RFK38B-7.5-90B14/SS	7,5	7,6	1 051,60 €
	RFK38B-10-80B14/SS	RFK38B-10-90B14/SS	10	10,5	1 051,60 €
	RFK38B-12-80B14/SS	RFK38B-12-90B14/SS	12,5	12,67	1 051,60 €
RFK38B-15-71B14/SS	RFK38B-15-80B14/SS	RFK38B-15-90B14/SS	15	14,67	1 051,60 €
RFK38B-20-71B14/SS	RFK38B-20-80B14/SS	RFK38B-20-90B14/SS	20	20,25	1 051,60 €
RFK38B-25-71B14/SS	RFK38B-25-80B14/SS	RFK38B-25-90B14/SS	25	24,44	1 051,60 €
RFK38B-30-71B14/SS	RFK38B-30-80B14/SS	RFK38B-30-90B14/SS	30	30,31	1 051,60 €
RFK38B-40-71B14/SS	RFK38B-40-80B14/SS		40	39,29	1 051,60 €
RFK38B-50-71B14/SS	RFK38B-50-80B14/SS		50	48,71	1 051,60 €
RFK38B-60-71B14/SS	RFK38B-60-80B14/SS		60	60,5	1 051,60 €

All dimensions in mm

## Our other products



BOX-WM

Box set of washer - DIN125, Box set of steel washers




PTA100

Articulated levelling foot, pressed base Ø100, Ø 100



GDR880

Straight track for slat top chain, Ranges 880 and 881



CFC

Spring loaded position switch, Electric contact



PSG25S

Spur gear - precision range, Stainless steel 303



TK\_UUOP

Topball self-aligning linear bearing, Topball self-aligning



H2

Crossed helical gear crossed axis at 90°, Machined plastic (delrin)



S\_2RS

Deep groove ball bearing, Stainless steel



ACL-PLAngle

Joining plate for aluminium profile, Angle connection



CPAS

Stay with safety catch, Opens upward



GTCS5

Belt tensioner, For use in hostile environments



PWC

Powercoil thread inserts, Kit Powercoil - with or without insertion ...

## Complementary products



DER71

Stainless steel AC asynchronous motor 0.25 à 0.37kW, 0.25 to 0.37kW



DER80

Stainless steel AC asynchronous motor 0.55 - 0.75kW, 0.55 to 0.75kW



DER90

Stainless steel AC asynchronous motor 1.1 - 1.5kW, 1.1 to 1.5kW



RFKfp

Stainless steel gearbox - accessories, Mounting bracket