

High temperature wheel



RHT

Load up to 250kg

- Phenolic resin castor wheel
- Slide bearings
- Working temp.: -30°C to +280°C

Advantages

- Large storage capacity
- Resists high temperatures



ØD



B



C



ØA

DISCOUNTS

Qty	1+	5+	15+
Disc. Price		-5%	On request

Part number	ØD	B	C	ØA	Load capacity (kg)	Price per unit	
						1 to 4	
RHT80-35/ML	80	35	40	12	125		16,27 €
RHT100-35/ML	100	35	40	12	150		16,47 €
RHT125-40/ML	125	40	48	15	200		59,92 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



Stainless steel spherical bearing, Stainless steel / PTFE



Joining plate for aluminium profile, Joint plate - 90x90 mm



Horizontal stirrup toggle clamp, Horizontal stirrup clamp - steel



Manually tightened wing nut DIN315, Brass DIN 315



Threaded spherical knob, With brass insert



Universal 90° support clamp, Universal 90° support clamp



Slat top chain acetal, Large range 821



Single rod clip, Round



Storage bin, 8mm



V-rail guidance Simple Select® system, Rail with



Moulded plastic bevel gear (nylon), 1:1



60mm rubber wheel for conveyor belt, Rubber

Complementary products



High Temperature Castor, up to 200kg



High Temperature Castor, up to 200kg



High Temperature Castor, up to 200kg



High Temperature Castor, up to 200kg