

High temperature wheel



RHT

Load up to 250kg

- Phenolic resin castor wheel
- Slide bearings
- Working temp.: -30°C to +280°C

Advantages

- Large storage capacity
- Resists high temperatures



ØD



B



C



ØA

DISCOUNTS

| | | | |
|-------------|----|-----|------------|
| Qty | 1+ | 5+ | 15+ |
| Disc. Price | | -5% | On request |

| Part number | ØD | B | C | ØA | Load capacity (kg) | Price per unit | |
|--------------|-----|----|----|----|--------------------|----------------|---------|
| | | | | | | 1 to 4 | |
| RHT80-35/ML | 80 | 35 | 40 | 12 | 125 | | 16,27 € |
| RHT100-35/ML | 100 | 35 | 40 | 12 | 150 | | 16,47 € |
| RHT125-40/ML | 125 | 40 | 48 | 15 | 200 | | 59,92 € |

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



HTD5M_09

HTD Heavy duty timing pulley, HTD5 Aluminium



T2.5-ECO

T type timing pulley, Economy range - T2.5 aluminium



E40

Right angle helical reducers, from 2.30 to 20 Nm



HLC24

Right angle spiro bevel gearbox, Up to 78Nm



DOG111

Motor-gearbox 12V and 24V DC, from 1.5 to 6 Nm



CAP805

Slat top chain stainless steel, Large range 805



HRV

V-rail guidance Simple Select® system, Rail with carriage



PW_PWG3

Worm - precision range, Steel




LVT

Miniature motorised actuator 2A, 2 ampers



T5M_T10M

T type timing belt per metre, T5 Steel cored



IN2

Internal gear, Machined plastic



RCX-6

Spherical tilt washer - DIN6319, concave

Complementary products



RHTtcss

High Temperature Castor, up to 200kg



RHTtcss

High Temperature Castor, up to 200kg



RHTplss

High Temperature Castor, up to 200kg



RHTplss

High Temperature Castor, up to 200kg