

# High temperature wheel



## RHT

## Load up to 250kg

- Phenolic resin castor wheel
- Slide bearings
- Working temp.: -30°C to +280°C

### Advantages

- Large storage capacity
- Resists high temperatures



ØD



B



C



ØA

### DISCOUNTS

Qty	1+	5+	15+
Disc. Price		-5%	On request

Part number	ØD	B	C	ØA	Load capacity (kg)	Price per unit	
						1 to 4	
RHT80-35/ML	80	35	40	12	125		16,27 €
RHT100-35/ML	100	35	40	12	150		16,47 €
RHT125-40/ML	125	40	48	15	200		59,92 €

Dimensions in mm

**HPC**

WEB  
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

## Our other products



RAS  
90°ball and socket joints DIN71802, Steel



DOMI50  
Accessories, Turntable



PMB  
Anti-vibration machine mount, Oval base plate



ZB  
Shaft for linear guides, Hardened ground stainless steel



BPQ  
Quadro linear ball bearing unit, Included 4 linear ball bearings



PR125rehausse  
Extension for articulated foot Ø123, articulated foot PR125



CHNrb  
Warning chain with red and white links, Steel




ACL-FPA  
Panel mounting block for aluminium structures, Support block




HW\_HT  
Half-rail guide, Wheel



LVT  
Miniature motorised actuator 4A, 4 amperes



CFC  
Spring loaded position switch, Electric



BFM  
Flanged bronze nut, Bronze - 1 thread

## Complementary products



RHTtcss  
High Temperature Castor, up to 200kg



RHTtcss  
High Temperature Castor, up to 200kg



RHTplss  
High Temperature Castor, up to 200kg



RHTplss  
High Temperature Castor, up to 200kg