

High Temperature Castors



RHTPLSS

Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:
304 stainless steel sheet
Polyamide wheel (see RHT)
- Working temp.: -30°C to +280°C



Fixed



Swivel

Advantages

- Large storage capacity
- Resists high temperatures



Double locking swivel



ØD



B



H



L



M



T



ØK

DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	On request	

Part number	ØD	B	H	L	M	ØT	Circle interference ØK	Load maximum (kg)	Price per unit 1 to 4
Fixed									
RHT80/PL/F/SS	80	35	105	115x83	80x60	11x9		125	32,70 €
RHT100/PL/F/SS	100	35	126	115x83	80x60	11x9		150	33,33 €
RHT125/PL/F/SS	125	40	153	115x83	80x60	11x9		200	76,05 €
Swivel									
RHT80/PL/P/SS	80	35	105	115x83	80x60	11x9	173	125	40,77 €
RHT100/PL/P/SS	100	35	126	115x83	80x60	11x9	193	150	41,93 €
RHT125/PL/P/SS	125	40	153	115x83	80x60	11x9	221	200	85,28 €
Double locking swivel									
RHT80/PL/PDB/SS	80	35	105	115x83	80x60	11x9	293	125	49,34 €
RHT100/PL/PDB/SS	100	35	126	115x83	80x60	11x9	293	150	50,50 €
RHT125/PL/PDB/SS	125	40	153	115x83	80x60	11x9	293	200	93,85 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15€/min + prix appel

Our other products



ACLEPP

Right angled bracket for aluminium profile, 4 holes



PGNT

Thermoplastic T handle, With threaded insert



KB_WW

Closed linear precision bearing, Economy range



PW_PWG25

Wheel - precision range, Bronze



NKXR

Combined bearing without inner ring, Needle and cylindrical rollers



GAL21

Conveyor wheel, Plastic




RTN

BoWex® curved tooth gear coupling, Nylon



DIL

Lever operated locking bolt, lever clamp



PSG15

Spur gear - precision range, Stainless steel 303




PF60

Worm and wheel gear reducer, up to 118 Nm



SHW

Plain washer, Steel



SLVHlok

Vertical toggle clamp, Vertical toggle clamp / horizontal foot

Complementary products



RHTtcss

High Temperature Castor, up to 200kg



RHTtcss

High Temperature Castor, up to 200kg



RHT

High Temperature wheel, up to 200kg



RHTplss

High Temperature Castor, up to 200kg