

# High Temperature Castor with central hole

## RHTTCSS

## Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:  
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:  
304 stainless steel sheet  
Polyamide wheel (see RHT)  
Working temp. range: -30°C to +280°C

### Advantages

- Large storage capacity
- Resists high temperatures



Swivel



Double locking swivel



ØD



B



H



ØE



ØK

### DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	On request	

Part number	ØD	B	H	ØE	Circle interference ØK	Load maximum (kg)	Price per unit 1 to 4
<b>Swivel</b>							
RHT80/TC/P/SS	80	35	105	12	173	125	40,77 €
RHT100/TC/P/SS	100	35	126	12	193	150	41,93 €
RHT125/TC/P/SS	125	40	153	12	221	200	85,28 €
<b>Double locking swivel</b>							
RHT80/PL/P/SS	80	35	105	12	173	125	49,34 €
RHT100/PL/P/SS	100	35	126	12	193	150	50,50 €
RHT125/PL/P/SS	125	40	153	12	221	200	93,85 €

Dimensions in mm

## Our other products



UTKpwrr

V shaped channel  
UtiliTrak®, V rail



CSS

Spherical bushing,  
Steel / self lubricating  
steel



CMAss

Eye bolt stainless  
steel, Stainless steel



IN1

Internal gear, Steel  
20NCD2



ACLRP

Wheel for aluminium  
profile, Integrated  
bearing



BLHB60

Right angled gearbox,  
bored shafts, up to 70  
Nm



DOMI30

Connecting kits, XZ  
linking kit



SH4

Parallel axis helical  
gear, Steel 20NCD2



INS

Self tapping steel  
insert, Steel




BOX-TOR-C

Box set of Nitrile O-  
rings in nitrile, 3.00 x  
1.50mm to 30.20 x



AT5P\_AT10P

Connecting plate for  
AT type timing belts,  
AT10



T5M\_T10M

T type timing belt per  
metre, T5 Steel cored  
polyurethane

## Complementary products



RHTtcss

High Temperature  
Castor, up to 200kg



RHT

High Temperature  
wheel, up to 200kg



RHTplss

High Temperature  
Castor, up to 200kg



RHTplss

High Temperature  
Castor, up to 200kg