

High Temperature Castor with central hole

RHTTCSS

Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:
304 stainless steel sheet
Polyamide wheel (see RHT)
Working temp. range: -30°C to +280°C

Advantages

- Large storage capacity
- Resists high temperatures



Swivel



Double locking swivel



ØD



B



H



ØE



ØK

DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	On request	

Part number	ØD	B	H	ØE	Circle interference ØK	Load maximum (kg)	Price per unit 1 to 4
Swivel							
RHT80/TC/P/SS	80	35	105	12	173	125	40,77 €
RHT100/TC/P/SS	100	35	126	12	193	150	41,93 €
RHT125/TC/P/SS	125	40	153	12	221	200	85,28 €
Double locking swivel							
RHT80/PL/P/SS	80	35	105	12	173	125	49,34 €
RHT100/PL/P/SS	100	35	126	12	193	150	50,50 €
RHT125/PL/P/SS	125	40	153	12	221	200	93,85 €

Dimensions in mm

HPC

WEB
04/2020

www.hpceurope.com

Tél: 0 825 88 5000 Service 0,15 €/min + prix appel

Our other products



LWL

Linear ball slide -
Stainless steel balls,
Rail - from 514 N to
1670...



VTLB

Three-lobed knob,
Thermoplastic / Brass
or stainless steel
insert



MCL

Cylindrical threaded
sleeve, Cylindrical -
stainless steel



PRES

Manual workbench
press accessory for
PRES-3HR end
PRES-4HR, Set of s...



PRF_PIV

Internal hinge pin for
aluminium profile,
Internal hinge pin



GMK17_RG

Joint for guiding
profile, Rounded




SH0

Parallel axis helical
gear, Steel 20NCD2



PO

Pull handle - Multi-
sector, Tapped
recessed insert



RPPM

RPP type belt per
metre, RPP5 Steel
cored polyurethane



CTZYSS

Stainless steel diablo
shaped elasto mount,
Stainless steel



PRF_FIX_ANG

Fastener for
aluminium profile,
Angular joint



PTA80ssEB

Articulated foot with
sheet metal base
Ø80, Articulated foot

Complementary products



RHTtcss

High Temperature
Castor, up to 200kg



RHT

High Temperature
wheel, up to 200kg



RHTplss

High Temperature
Castor, up to 200kg



RHTplss

High Temperature
Castor, up to 200kg