

High Temperature Castor with central hole

RHTTCSS

Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:
304 stainless steel sheet
Polyamide wheel (see RHT)
Working temp. range: -30°C to +280°C

Advantages

- Large storage capacity
- Resists high temperatures



Swivel



Double locking swivel



ØD



B



H



ØE



ØK

DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	On request	

Part number	ØD	B	H	ØE	Circle interference ØK	Load maximum (kg)	Price per unit 1 to 4
Swivel							
RHT80/TC/P/SS	80	35	105	12	173	125	40,77 €
RHT100/TC/P/SS	100	35	126	12	193	150	41,93 €
RHT125/TC/P/SS	125	40	153	12	221	200	85,28 €
Double locking swivel							
RHT80/PL/P/SS	80	35	105	12	173	125	49,34 €
RHT100/PL/P/SS	100	35	126	12	193	150	50,50 €
RHT125/PL/P/SS	125	40	153	12	221	200	93,85 €

Dimensions in mm

Our other products



UTKpwrr

V shaped channel
UtiliTrak®, V rail



CSS

Spherical bushing,
Steel / self lubricating
steel



CMAss

Eye bolt stainless
steel, Stainless steel



IN1

Internal gear, Steel
20NCD2



ACLRP

Wheel for aluminium
profile, Integrated
bearing



BLHB60

Right angled gearbox,
bored shafts, up to 70
Nm



DOMI30

Connecting kits, XZ
linking kit



SH4

Parallel axis helical
gear, Steel 20NCD2



INS

Self tapping steel
insert, Steel




BOX-TOR-C

Box set of Nitrile O-
rings in nitrile, 3.00 x
1.50mm to 30.20 x



AT5P_AT10P

Connecting plate for
AT type timing belts,
AT10



T5M_T10M

T type timing belt per
metre, T5 Steel cored
polyurethane

Complementary products



RHTtcss

High Temperature
Castor, up to 200kg



RHT

High Temperature
wheel, up to 200kg



RHTplss

High Temperature
Castor, up to 200kg



RHTplss

High Temperature
Castor, up to 200kg