

Locking castor with mounting plate

For loads up to 1000kg

RIM



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C



Adjusting nut

Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate square
- Wheel: Black polyamide Shore D 70



DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	L	M	ØT	Swivel interference ØK	Load (kg)	Price each
										1 to 5
RIM42-60/PLE	42	20	71	81	55x55	42x42	6,5	84	60	46,66 €
RIM50-280/PLE	50	25	82	92	73x73	58x58	7	101	280	74,11 €
RIM63-550/PLE	63	28	103	118	90x90	70x70	9	125	550	100,71 €
RIM75-800/PLE	75	30	120	132	95x95	70x70	11	142	800	111,33 €
RIM75-1000/PLE	75	30	120	132	95x95	70x70	11	142	1000	132,76 €

Dimensions in mm

Our other products



PSG08S

Spur gear - precision range, Stainless steel 316



V3RA

3-spoked handwheel without handle, Polyamide



BLHM50

Right angled gearbox, double output shafts, up to 30 Nm



RURt

Swivel castor with central hole, Polyurethane - Aluminium rim (Free)



CHT

Asynchronous AC Motor 1.1 to 1.85kW, 1.1 to 1.85kW



CHT

Asynchronous AC motor 0.12 to 0.22kW, 0.12 to 0.22kW



G0

Steel spur gear, Steel 20NCD2



CHMX_CHMDX

Shaft for worm and wheel reducer CHMR and CHM, CHMR and CHM gearbox...



PRF-GPB

Guide for aluminium profile, Rail for 8mm



EKN

Bellows coupling Gerwah®, from 0.5 to



H0

Crossed helical gear crossed axis at 90°,



PW_PWG25

Wheel - precision range, Bronze

Complementary products



RIMtce

Locking castor, with central hole



PDR-RD

Mounting feet with integrated castors, Offset castor