

Locking castor with central hole



RIM

For loads up to 1000kg



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C

Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70



Adjusting nut



DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 5
RIM42-60/TCE	42	20	71	81	M8	84	60	46,66 €
RIM50-280/TCE	50	25	82	92	M12	101	280	74,11 €
RIM63-550/TCE	63	28	103	118	M12	125	550	100,71 €
RIM75-800/TCE	75	30	120	132	M16	142	800	111,33 €
RIM75-1000/TCE	75	30	120	132	M16	142	1000	132,76 €

Dimensions in mm

Our other products



WS16
Drylin® W rail, Rail



BABreceptacle
Ball pin socket, Socket



BLH60
Right angled gearbox,
from 19 to 70 Nm



SA_SAKH
Housing for linear
bearing, Closed - light
load



PW_PWG05
Worm - precision
range, Steel



GCA
Linch pin, Linch



SCA
Flat cable clamp,
Steel



UGAC_UGET
Connection for
threaded actuator
rod, Connection for
threaded actuat...



CHB
Feet, For CHB gearbox



WJRM
Drylin® W hybrid
bearing block, Hybrid
bearings



LRR
Spring loaded latch,
Spring loaded latch



ATZYSS
Stainless steel diabolo
shaped elasto mount,
Stainless steel

Complementary products



RIMple
Locking castor, with
mounting plate



PDR-RD
Mounting feet with
integrated castors,
Offset castor