


Ring Gears

Module 2 to 3

Steel

- **Steel Ring Gears (Spur Gears)**
- Precision grade JIS grade N9
(JIS B1702-1: 1998)
- Material:
Steel S45C



DISCOUNTS

Qty	1+	2+
Disc.	List	On request

Part number	Module	Z Teeth	ØP PCD	ØD Outside	ØA Bore	E	Mass (kg)	Price each 1 to 5
RING2-120	2	120	240	244	194	20	2,46	
RING2-200	2	200	400	404	354	20	4,28	
RING2,5-120	2,5	120	300	305	245	25	4,62	
RING2,5-200	2,5	200	500	505	445	25	8,01	
RING3-120	3	120	360	366	296	30	7,77	
RING3-160	3	160	480	486	416	30	10,60	

Dimensions in mm

Our other products



PPG
Indexing plunger with flange, With horizontal mounting flange



DOMI50
Accessories, Turntable



ZDB
Machined plastic bevel gear , 2:1



AC
Strike for toggle latch, 15mm



BLHM40
Right angled gearbox, double output shafts, up to 10.3 Nm



BAPTBS
Clamping pin for blind hole, Stainless steel 303



PPS
Lifting ring, Universal threaded




SH1
Parallel axis helical gear, Machined plastic (delrin)




PW_PWG3
Wheel - precision range, Bronze



NPTR10
Adjustable cross clamp, Adjustable



CFC
Spring loaded position switch, Electric contact



CFC
Spring loaded position switch, Electric contact

Complementary products