



Cam follower without axial guide


Without interior ring

IKO RNAS


- For shaft diameters from 7mm to 60mm
- With external cylindrical cage
- Without wiper seals
- Material: steel
- Working temperature: -20°C to +120°C

Assembly

- Use with rails with a minimum hardness of 40 HRC
- Tolerance of shaft: g6, h6
- Shaft hardness: 58-64 HRC, Ra 0.2



Typical application



DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number	Shaft Ø	ØD	C	Static load Co (N)	Dynamic load C (N)	Weight (g)	Stock*	Price each 1 to 5
RNAS-5	07	16	07,8	2390	2710	8,9	✓	15,60 €
RNAS-6	10	19	09,8	4550	4160	13,9	✓	16,92 €
RNAS-8	12	24	09,8	5890	5650	23,5	✓	17,63 €
RNAS-10	14	30	11,8	9680	9790	42,5	✓	18,28 €
RNAS-12	16	32	11,8	10900	10500	49,5	✓	19,42 €
RNAS-15	20	35	11,8	14300	12400	50,0	✓	20,29 €
RNAS-17	22	40	15,8	20900	17600	90,0	-	20,19 €
RNAS-20	25	47	15,8	24500	19400	135,0	✓	22,32 €
RNAS-25	30	52	15,8	28400	20800	152,0	-	25,06 €
RNAS-30	38	62	19,8	45400	30500	255,0	-	28,06 €
RNAS-35	42	72	19,8	50600	32400	375,0	-	30,95 €
RNAS-40	50	80	19,8	61100	35900	420,0	-	36,48 €
RNAS-45	55	85	19,8	66400	37400	460,0	-	37,43 €
RNAS-50	60	90	19,8	71700	38900	500,0	-	41,75 €

*Depending on availability - Dimensions in mm

Our other products



LC

Friction clutch, 30 to 240 Nm




BTCW

Cap for square tube to be welded, To be welded




CM

Tools Hygienic Usit® and Hygienic Design®, Combination spanner



NK80

Drylin®N miniature guiding system, Width 80mm



LSM

Stainless steel 316L leadscrew, Stainless steel - 1 thread



RTE

Rotex®, jaw coupling, Aluminium



PSG35

Spur gear - precision range, Stainless steel 303



MFBC

Flexible Bellows coupling, Aluminium and Bronze - with clamping jaw



LWH

High rigidity linear slide, Rail - from 9320




CLG3

Moulded plastic spur gear, Moulded plastic



TMR

Rigid manual tensioner, Adjustable



B

Steel bevel gear, 1:1

Complementary products



NAST

Cam follower without axial guide, With interior ring



CF

Cam follower, Standard - steel