



# Cam follower without axial guide


Without interior ring

**IKO** RNAS


- For shaft diameters from 7mm to 60mm
- With external cylindrical cage
- Without wiper seals
- Material: steel
- Working temperature: -20°C to +120°C

## Assembly

- Use with rails with a minimum hardness of 40 HRC
- Tolerance of shaft: g6, h6
- Shaft hardness: 58-64 HRC, Ra 0.2



Typical application



## DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Part number	Shaft Ø	ØD	C	Static load Co (N)	Dynamic load C (N)	Weight (g)	Stock*	Price each 1 to 5
RNAS-5	07	16	07,8	2390	2710	8,9	✓	15,60 €
RNAS-6	10	19	09,8	4550	4160	13,9	✓	16,92 €
RNAS-8	12	24	09,8	5890	5650	23,5	✓	17,63 €
RNAS-10	14	30	11,8	9680	9790	42,5	✓	18,28 €
RNAS-12	16	32	11,8	10900	10500	49,5	✓	19,42 €
RNAS-15	20	35	11,8	14300	12400	50,0	✓	20,29 €
RNAS-17	22	40	15,8	20900	17600	90,0	-	20,19 €
RNAS-20	25	47	15,8	24500	19400	135,0	✓	22,32 €
RNAS-25	30	52	15,8	28400	20800	152,0	-	25,06 €
RNAS-30	38	62	19,8	45400	30500	255,0	-	28,06 €
RNAS-35	42	72	19,8	50600	32400	375,0	-	30,95 €
RNAS-40	50	80	19,8	61100	35900	420,0	-	36,48 €
RNAS-45	55	85	19,8	66400	37400	460,0	-	37,43 €
RNAS-50	60	90	19,8	71700	38900	500,0	-	41,75 €

\*Depending on availability - Dimensions in mm

## Our other products




ACLEFS  
Floor anchor for  
aluminium profile,  
Adjustable



LRX  
Linear roller slide,  
Chariot - from 9410 N  
to 101000 N



PSP  
Support profile, Panel  
support



LAT2  
2A motorised linear  
actuator, 2 amperes



KKSS  
Rounded end feather  
key, Stainless steel



EBH  
Cap nut Hygienic  
Design®, With collar



P30  
Worm and wheel gear  
reducer, up to 8.80  
Nm



DOMI30  
Accessories, Plate




DOMI50  
Domino 50 adjustable  
slide, Slide DOMILINE  
50



HW\_HT  
Half-rail guide, Rail



PRF\_VTM  
Hammerhead screw,  
Hammerhead screw



M2  
Worm and wheel set,  
Machined plastic  
(delrin)

## Complementary products



NAST  
Cam follower without  
axial guide, With  
interior ring



CF  
Cam follower,  
Standard - steel