

Polyamide wheel

For loads up to 600kg

RPC

- Light coloured Polyamide wheel
- Smooth central bore
- Working temperature range: -30°C to +80°C

Advantages

- Shock and abrasion resistant
- Does not stain floors
- Does not mark floors
- Resists most chemical agents
- Low rolling resistance
- For solid and hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



For smooth surfaces



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RPC60-31/ML	60	31	40	12	200	✓	2,06 €
RPC80-32/ML	80	32	40	12	250	✓	2,14 €
RPC100-32/ML	100	32	40	12	300	✓	2,83 €
RPC100-35/ML	100	35	48	15	350	-	9,76 €
RPC125-36/ML	125	36	50	15	350	-	5,16 €
RPC125-41/ML	125	41	59	20	400	-	10,93 €
RPC150-37/ML	150	37	49	15	400	-	8,19 €
RPC160-40/ML	160	40	58	20	500	-	22,48 €
RPC200-50/ML	200	50	58	20	600	-	24,41 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Fax


cial2@hpceurope.com

HPC

SUPPLEMENT 2019


265

Our other products



CFC

Spring loaded position switch, Electric contact



CT

Telescopic universal joint, Normal duty



CAP881

Side flexing slim slat top chain stainless steel, Narrow range 881



KK

Rounded end feather key, Steel



BOX-TOR-DRING

Box set of Nitrile D-rings NBR90Sh A, Flange seals



BAN

Angular clamp, Adjustable



ACM_DZ

Clip for bonnet fastener, Clip



CFUURSS

Cam follower stainless steel, Standard - stainless steel



CHB

Double output shaft, For CHB gearbox



BABFCFO

Ball pin socket, Mounting collar with a oval flange



PRES4HR

Manual workbench press, Force up to 600kg



VTA

Vari-Tork® slip friction clutch, 0.53 to 1.32 Nm

Complementary products



RPCpl

Fixed castor with plate, Steel - Polyamide



RPCpl

Swivel castor with plate, Steel - Polyamide



RPCpl

Swivel castor with double brake, Steel - Polyamide



RPCplss

Swivel castor with plate, Stainless steel - Polyamide