

Polyamide wheel

For loads up to 600kg

RPC

- Light coloured Polyamide wheel
- Smooth central bore
- Working temperature range: -30°C to +80°C

Advantages

- Shock and abrasion resistant
- Does not stain floors
- Does not mark floors
- Resists most chemical agents
- Low rolling resistance
- For solid and hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



For smooth surfaces



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RPC60-31/ML	60	31	40	12	200	✓	2,06 €
RPC80-32/ML	80	32	40	12	250	✓	2,14 €
RPC100-32/ML	100	32	40	12	300	✓	2,83 €
RPC100-35/ML	100	35	48	15	350	-	9,76 €
RPC125-36/ML	125	36	50	15	350	-	5,16 €
RPC125-41/ML	125	41	59	20	400	-	10,93 €
RPC150-37/ML	150	37	49	15	400	-	8,19 €
RPC160-40/ML	160	40	58	20	500	-	22,48 €
RPC200-50/ML	200	50	58	20	600	-	24,41 €

Dimensions in mm

Fax **0 825 88 6000**
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019


265

Our other products



HLA24

Right angle spiro bevel gearbox, Up to 78Nm



RPP14

RPP heavy duty timing belt, RPP14



LVT

Miniature motorised actuator 1A, 1 amper



PLC_PLT

Magnetic stud with threaded hole, With threaded hole



gt64r

Rotating bent lever with spring, Increased fitting tolerances



DFG

Flat suction cup, silicon




NPTR10

Adjustable cross clamp, Adjustable



PSG1

Spur gear - precision range, Pre-hardened Steel 35NCD6



M2

Worm and wheel set, Machined plastic (delrin)



PNA_R

PERIFLEX elastic coupling, Replacement tyre



ZG1

Plastic spur gear, Machined plastic (delrin)



FF50

Offset spur gear reducer, from 111 to 425 Nm

Complementary products



RPCpl

Fixed castor with plate, Steel - Polyamide



RPCpl

Swivel castor with plate, Steel - Polyamide



RPCpl

Swivel castor with double brake, Steel - Polyamide



RPCplss

Swivel castor with plate, Stainless steel - Polyamide