

Polyamide wheel

For loads up to 600kg

RPC

- Light coloured Polyamide wheel
- Smooth central bore
- Working temperature range: -30°C to +80°C

Advantages

- Shock and abrasion resistant
- Does not stain floors
- Does not mark floors
- Resists most chemical agents
- Low rolling resistance
- For solid and hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



For smooth surfaces



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RPC60-31/ML	60	31	40	12	200	✓	2,06 €
RPC80-32/ML	80	32	40	12	250	✓	2,14 €
RPC100-32/ML	100	32	40	12	300	✓	2,83 €
RPC100-35/ML	100	35	48	15	350	-	9,76 €
RPC125-36/ML	125	36	50	15	350	-	5,16 €
RPC125-41/ML	125	41	59	20	400	-	10,93 €
RPC150-37/ML	150	37	49	15	400	-	8,19 €
RPC160-40/ML	160	40	58	20	500	-	22,48 €
RPC200-50/ML	200	50	58	20	600	-	24,41 €

Dimensions in mm

Fax **0 825 88 6000**
Service 0,15 € / min
+ prix appel

Our other products



PRF-P
Aluminium profile feet support, For feet or casters



SVT5
Screwjack with travelling screw, with translating screw



PRS80
Stainless steel articulated foot Ø80, Ø 80



IN1
Internal gear, Steel 20NCD2



PGMT
Pull handle, Steel



ERF
Quick fitting threaded cable terminal, Cable terminal with threaded ...



PR40
Articulated foot Ø40, Ø 40



CHARcav
Spring hinge, to install




SHWbr
Washer - DIN125, Brass



RFVfp
Stainless steel worm and wheel gearboxes,



ESCON
Speed controller 5A, 5 A



LAT1
1A motorised linear actuator, 1 ampere

Complementary products



RPCpl
Fixed castor with plate, Steel - Polyamide



RPCpl
Swivel castor with plate, Steel - Polyamide



RPCpl
Swivel castor with double brake, Steel - Polyamide



RPCplss
Swivel castor with plate, Stainless steel - Polyamide