

Polyamide wheel

For loads up to 600kg

RPC

- Light coloured Polyamide wheel
- Smooth central bore
- Working temperature range: -30°C to +80°C

Advantages

- Shock and abrasion resistant
- Does not stain floors
- Does not mark floors
- Resists most chemical agents
- Low rolling resistance
- For solid and hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



For smooth surfaces



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RPC60-31/ML	60	31	40	12	200	✓	2,06 €
RPC80-32/ML	80	32	40	12	250	✓	2,14 €
RPC100-32/ML	100	32	40	12	300	✓	2,83 €
RPC100-35/ML	100	35	48	15	350	-	9,76 €
RPC125-36/ML	125	36	50	15	350	-	5,16 €
RPC125-41/ML	125	41	59	20	400	-	10,93 €
RPC150-37/ML	150	37	49	15	400	-	8,19 €
RPC160-40/ML	160	40	58	20	500	-	22,48 €
RPC200-50/ML	200	50	58	20	600	-	24,41 €

Dimensions in mm

Fax **0 825 88 6000**
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019


265

Our other products



T10courroie

T type timing belt,
T10 Steel cored
polyurethane



B

Steel bevel gear, 1:1



PCS62K

Chain sprocket with
hardened teeth,
15.875mm (DIN10B-1)



LVT

Miniature motorised
actuator 4A, 4 ampers



S_2RS

Deep groove ball
bearing, Stainless
steel



PSG08S

Spur gear - precision
range, Stainless steel
316



RURt

Swivel castor with
central hole,
Polyurethane -
Aluminium rim (Free



M1

Worm and wheel set,
Machined plastic
(delrin)



CLG3

Moulded plastic spur
gear, Moulded plastic
(nylon)



CSSSS

Stainless steel
spherical bearing,
Stainless steel / PTFE



CHAuss

Screwed hinge, 270°



BLHM60

Right angled gearbox,
double output shafts,
up to 70 Nm

Complementary products



RPCpl

Fixed castor with
plate, Steel -
Polyamide



RPCpl

Swivel castor with
plate, Steel -
Polyamide



RPCpl

Swivel castor with
double brake, Steel -
Polyamide



RPCplss

Swivel castor with
plate, Stainless steel -
Polyamide