


RPP timing belt

Pitch RPP14 Chloroprene rubber belt with glass fibre tension members

- To be used with HTD14M pulley
- Pitch 14mm
- Efficiency: up to 98%
- Materials:
chloroprene rubber reinforced
with glass fibres
nylon protective film



Advantages

- Shock-resistant
- The RPP parabolic tooth profile gives a higher torque capability and greater resistance to tooth jump

Accessories

- Pulleys HTD14M
- Belt tension rollers GTC

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-7%	On request

Part number	Length	N° of teeth	Price each 1 to 5 for a width of	
			55mm	85mm
RPP14/966	966	69	166,55 €	272,45 €
RPP14/994	994	71	167,59 €	274,55 €
RPP14/1092	1092	78	168,45 €	276,76 €
RPP14/1106	1106	79	170,72 €	280,43 €
RPP14/1190	1190	85	179,54 €	281,48 €
RPP14/1260	1260	90	180,40 €	282,67 €
RPP14/1288	1288	92	182,31 €	285,80 €
RPP14/1344	1344	96	188,58 €	298,27 €
RPP14/1400	1400	100	196,33 €	307,63 €
RPP14/1442	1442	103	202,25 €	316,83 €
RPP14/1568	1568	112	208,83 €	324,81 €
RPP14/1610	1610	115	214,40 €	333,48 €
RPP14/1764	1764	126	228,40 €	351,48 €
RPP14/1778	1778	127	231,03 €	354,27 €
RPP14/1848	1848	132	234,47 €	358,59 €
RPP14/1890	1890	135	239,67 €	366,73 €
RPP14/1904	1904	136	241,44 €	369,54 €
RPP14/1960	1960	140	242,98 €	371,22 €
RPP14/2100	2100	150	256,50 €	397,62 €
RPP14/2240	2240	160	264,13 €	401,24 €
RPP14/2310	2310	165	272,45 €	413,73 €
RPP14/2380	2380	170	275,22 €	427,08 €
RPP14/2450	2450	175	281,48 €	439,53 €
RPP14/2590	2590	185	289,30 €	452,03 €
RPP14/2660	2660	190	297,06 €	474,76 €
RPP14/2800	2800	200	312,68 €	499,70 €
RPP14/2968	2968	212	324,92 €	506,03 €
RPP14/3150	3150	225	337,12 €	512,32 €
RPP14/3360	3360	240	359,28 €	546,14 €
RPP14/3500	3500	250	362,40 €	563,82 €
RPP14/3850	3850	275	393,26 €	611,15 €
RPP14/3920	3920	280	394,65 €	622,23 €
RPP14/4326	4326	309	435,57 €	670,60 €
RPP14/4578	4578	327	456,19 €	703,74 €
RPP14/4956	4956	354	487,58 €	757,78 €

Dimensions in mm