

Free running wheel

RUR

For loads up to 350kg

- Light industrial wheel for loads up to 350kg
- Ball bearing hub
- Materials:
 - Polyurethane covered wheel 85 Shore
 - Aluminium rim
 - Working temperature range: -30 to +80°C

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	A	F	Max load (kg)	Price each 1 to 9
RUR80	80	40	12	41	180	17,79 €
RUR100	100	40	12	41	220	20,14 €
RUR125	125	40	15	41	260	21,97 €
RUR150	150	40	20	50	350	31,13 €

Dimensions in mm

Our other products



PC53755

Chain sprocket -
Stainless steel, 9.525
(DIN 06B-1)



PSG25

Spur gear - precision
range, Pre-hardened
Steel 35NCD6



AC156-157

Strike for toggle latch,
25.5mm



M0

Worm and wheel set,
Bronze



GE1006

Elastic ringed latch,
Hooks into a slot



E50

Right angle helical
reducers, from 3 to 41
Nm




HBM

Adjustment bushing
for half-rail guide,
Adjustment bushing



ETQ

Magnetic label holder
for aluminium profile,
Label holder



BETASS

Hitch pin, Hitch



DFG

Flat suction cup,
silicon



PF70

Worm and wheel gear
reducer, up to 164
Nm



SLV

Vertical toggle clamp,
Vertical Lever Clamp -
stainless steel

Complementary products



RURp

Fixed castor with
plate, Polyurethane -
Aluminium rim (Free
running)



RURp

Wheel pivoting with
plate, Polyurethane -
Aluminium rim (Free
running)



RURp

Swivel castor with
double brake,
Polyurethane -
Aluminium rim (Free
running)

...



RURt

Swivel castor with
central hole,
Polyurethane -
Aluminium rim (Free

