

Free running wheel

RUR

For loads up to 350kg

- Light industrial wheel for loads up to 350kg
- Ball bearing hub
- Materials:
 - Polyurethane covered wheel 85 Shore
 - Aluminium rim
 - Working temperature range: -30 to +80°C

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	A	F	Max load (kg)	Price each 1 to 9
RUR80	80	40	12	41	180	17,79 €
RUR100	100	40	12	41	220	20,14 €
RUR125	125	40	15	41	260	21,97 €
RUR150	150	40	20	50	350	31,13 €

Dimensions in mm

Our other products



BOX-TOR-C

Box set of Nitrile O-rings in nitrile, 3.00 x 1.50mm to 30.20 x 3.00




CQA30

Accessory for adjustment slide-system, 30



PCLA_T

Technopolymer clamping lever - male, Plastic



TBV

Manual lifting tables, 7kg



NT63

Spur gear coaxial gearbox, from 8 to 20 Nm - In-line



PGMT

Pull handle, Steel



WS16

Drylin® W rail, Rail



H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2



PSG2

Spur gear - precision range, Pre-hardened Steel 35NCD6



NPTR_M

Adjustable cross clamp, Adjustable



SVG

Adjustable latch clamp with strike plate, Stroke from 118mm to 130,5mm



GLB

Small 6 lobe female handle, Technopolymer - Brass

Complementary products



RURp

Fixed castor with plate, Polyurethane - Aluminium rim (Free running)



RURp

Wheel pivoting with plate, Polyurethane - Aluminium rim (Free running)



RURp

Swivel castor with double brake, Polyurethane - Aluminium rim (Free running)

...



RURt

Swivel castor with
central hole,
Polyurethane -
Aluminium rim (Free

