

Free running wheel

RUR

For loads up to 350kg

- Light industrial wheel for loads up to 350kg
- Ball bearing hub
- Materials:
 - Polyurethane covered wheel 85 Shore
 - Aluminium rim
 - Working temperature range: -30 to +80°C

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	A	F	Max load (kg)	Price each 1 to 9
RUR80	80	40	12	41	180	17,79 €
RUR100	100	40	12	41	220	20,14 €
RUR125	125	40	15	41	260	21,97 €
RUR150	150	40	20	50	350	31,13 €

Dimensions in mm

Our other products



Adjustable shock absorber, Adjustable



Stainless steel cam lever, Female



Igubal® pillow block bearing, Polymer



Worm and wheel set, Machined plastic (delrin)



Self-centering flanged locking assembly, Medium/high torque



Stainless steel bevel gear, 2:1



Offset spur gear reducer, from 59 to 210 Nm



Square tube connector, Fixed angle



Shaft for linear guides, Hardened ground steel



Small 6 lobe threaded handle - male, Technopolymer -



Stainless steel U bolt, Stainless steel



Mini plain bearing ball transfer unit, For countersinking

Complementary products



Fixed castor with plate, Polyurethane - Aluminium rim (Free running)



Wheel pivoting with plate, Polyurethane - Aluminium rim (Free running)



Swivel castor with double brake, Polyurethane - Aluminium rim (Free running)

...



RURt

Swivel castor with
central hole,
Polyurethane -
Aluminium rim (Free

