

Free running wheel with mounting plate

For loads up to 350kg

RURP

- Light industrial castor for loads up to 350kg
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel 85 Shore
 - Aluminium rim
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Working temperature range: -30 to +80°C

Swivel with double lock




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

For rough floors

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Références	ØD	H	B	A	F	L	M	ØT	Swivel inter-ference ØK	Max load (kg)	Price each 1 to 9
Swivel											
RURP80/P	80	110	40	12	41	110x85	80x60	8	162	180	26,87 €
RURP100/P	100	127	40	12	41	110x85	80x60	8	184	220	29,51 €
RURP125/P	125	155	40	15	41	110x85	80x60	8	216	260	33,17 €
RURP150/P	150	181	40	20	50	110x85	80x60	8	244	350	42,85 €
Swivel with double brake											
RURP80/PDB	80	110	40	12	41	110x85	80x60	8	290	180	30,91 €
RURP100/PDB	100	127	40	12	41	110x85	80x60	8	290	220	33,76 €
RURP125/PDB	125	155	40	15	41	110x85	80x60	8	290	260	37,79 €
RURP150/PDB	150	181	40	20	50	110x85	80x60	8	290	350	47,31 €
Fixed											
RURP80/F	80	110	40	12	41	110x85	80x60	8	-	180	23,73 €
RURP100/F	100	127	40	12	41	110x85	80x60	8	-	220	26,21 €
RURP125/F	125	155	40	15	41	110x85	80x60	8	-	260	30,25 €
RURP150/F	150	181	40	20	50	110x85	80x60	8	-	350	40,35 €

Dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

277

Our other products



SSDB

Stainless steel bevel gear, 2:1



TK_UUOP

Topball self-aligning linear bearing, Topball self-aligning



LRX

Linear roller slide, Rail - from 9410 N to 101000 N



LR

Precision locknut, Precision locknut



STRIP1000

Sealing brush strip, 1m length



BABpss

301 Stainless steel ball pin, Stainless steel



GMK17_R

Round guide, Round guide for conical profile



SLB

Indexing plunger, stainless steel



HW_HT

Half-rail guide, Rail



LVT

Miniature motorised actuator 2A, 2 amperes



COA-COG

Surface mounting plate, Surface mounting plate for



P60

Worm and wheel gear reducer, up to 118 Nm

Complementary products



RPCpl

Swivel castor with double brake, Steel - Polyamide



RBNtc

Swivel castor with central hole, Steel - rubber - with double brake



RUR

Wheel, Polyurethane - Aluminium rim (Free running)



RPCplss

Swivel castor with double brake, Stainless steel - Polyamide