

Free running wheel with mounting plate

For loads up to 350kg

RURP

- Light industrial castor for loads up to 350kg
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel 85 Shore
 - Aluminium rim
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Working temperature range: -30 to +80°C

Swivel with double lock




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

For rough floors

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Références	ØD	H	B	A	F	L	M	ØT	Swivel inter-farence ØK	Max load (kg)	Price each 1 to 9
Swivel											
RURP80/P	80	110	40	12	41	110x85	80x60	8	162	180	26,87 €
RURP100/P	100	127	40	12	41	110x85	80x60	8	184	220	29,51 €
RURP125/P	125	155	40	15	41	110x85	80x60	8	216	260	33,17 €
RURP150/P	150	181	40	20	50	110x85	80x60	8	244	350	42,85 €
Swivel with double brake											
RURP80/PDB	80	110	40	12	41	110x85	80x60	8	290	180	30,91 €
RURP100/PDB	100	127	40	12	41	110x85	80x60	8	290	220	33,76 €
RURP125/PDB	125	155	40	15	41	110x85	80x60	8	290	260	37,79 €
RURP150/PDB	150	181	40	20	50	110x85	80x60	8	290	350	47,31 €
Fixed											
RURP80/F	80	110	40	12	41	110x85	80x60	8	-	180	23,73 €
RURP100/F	100	127	40	12	41	110x85	80x60	8	-	220	26,21 €
RURP125/F	125	155	40	15	41	110x85	80x60	8	-	260	30,25 €
RURP150/F	150	181	40	20	50	110x85	80x60	8	-	350	40,35 €

Dimensions in mm

0 825 88 6000

Service 0,15 € / min
+ prix appel

Fax

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

277

Our other products



PM2

Worm and wheel set,
Hardened steel



BLH40

Right angled gearbox,
from 3 to 10.30 Nm



MSP23

Masterplate®
glueable insert Ø23,
Cylindrical Ø23 with
tapped ins...



E60

Right angle helical
reducers, from 4.50 to
62 Nm



HTD5M_09

HTD Heavy duty
timing pulley, HTD5
Aluminium



DOMI50

Domino 50 adjustable
slide, Slide DOMILINE
50 with counter and
handw...



VQTplq

Quarter-turn clamp
lock - Clamping plate,
Wall mounting



ACLEFS

Floor anchor for
aluminium profile,
Standard




BCM_CC

Modular cylindrical
brush, Horsehair
bristles



M0

Worm and wheel set,
Hardened steel



PRF-GUM

Aluminium profile
anodising polisher,
Polishing block



BOX-WM

Box set of washer -
DIN125, Box set of
steel washers

Complementary products



RPCpl

Fixed castor with
plate, Steel -
Polyamide



RUR

Wheel, Polyurethane -
Aluminium rim (Free
running)



RBNpl

Fixed castor with
plate, Steel - rubber



RBGpl

Fixed castor with
plate, Steel - grey
rubber