

Free running wheel with central hole

RURT

For loads up to 350kg

- Light industrial castor for loads up to 350kg
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel, 85 Shore
 - Aluminium rim
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Working temperature range: -30 to +80°C

swivel

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc. List	-5%	On request	

Part number	ØD	H	B	A	F	E	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel									
RURT80/P	80	106	40	12	41	12	162	180	26,07 €
RURT100/P	100	126	40	12	41	12	184	220	28,42 €
RURT125/P	125	153	40	15	41	12	216	260	32,30 €
RURT150/P	150	180	40	20	50	12	244	350	32,30 €
Swivel with double brake									
RURT80/PDB	80	106	40	12	41	12	290	180	31,19 €
RURT100/PDB	100	126	40	12	41	12	290	220	33,83 €
RURT125/PDB	125	153	40	15	41	12	290	260	37,65 €
RURT150/PDB	150	180	40	20	50	12	290	350	50,18 €

Dimensions in mm

Our other products




BPTR

End cap for round tube, Standard



SH1

Parallel axis helical gear, Steel 20NCD2



TR

Spur round rack, Stainless steel - module 0,25-1,5



RT25ss

Self-centering flanged locking assembly, Medium/high torque



MDR_SS

Stainless steel Dee shackle with eye bolt, Stainless steel



AT5M AT10M

AT type timing belt per metre, AT5 Steel cored polyurethane



NK17

Drylin®N miniature guiding system, Width 17 mm



VB

Small 6 lobe threaded handle - female, Duroplast - Brass



ZG1

Plastic spur gear, Machined plastic (delrin)



CHMR110

Worm and wheel gear reducer, up to 980 Nm



GG3

Ground spur gear, Heat treated steel



PSG35

Spur gear - precision range, Stainless steel 303

Complementary products



RUR

Wheel, Polyurethane - Aluminium rim (Free running)



TSRTC

Stem support for caster, For swivel caster with central hole



RURp

Wheel pivoting with plate, Polyurethane - Aluminium rim (Free running)



RURp

Fixed castor with plate, Polyurethane - Aluminium rim (Free running)