

Free running wheel with central hole

RURT

For loads up to 350kg

- Light industrial castor for loads up to 350kg
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel, 85 Shore
 - Aluminium rim
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Working temperature range: -30 to +80°C

swivel

For rough floors




Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



DISCOUNTS

Qty	1+	10+	30+
Disc. List	-5%	On request	

Part number	ØD	H	B	A	F	E	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel									
RURT80/P	80	106	40	12	41	12	162	180	26,07 €
RURT100/P	100	126	40	12	41	12	184	220	28,42 €
RURT125/P	125	153	40	15	41	12	216	260	32,30 €
RURT150/P	150	180	40	20	50	12	244	350	32,30 €
Swivel with double brake									
RURT80/PDB	80	106	40	12	41	12	290	180	31,19 €
RURT100/PDB	100	126	40	12	41	12	290	220	33,83 €
RURT125/PDB	125	153	40	15	41	12	290	260	37,65 €
RURT150/PDB	150	180	40	20	50	12	290	350	50,18 €

Dimensions in mm

Our other products



T type timing pulley,
Economy range - T10
aluminium



Pressed steel base
rigid foot, Swivelling -
Ø80



Joining plate for
aluminium profile,
Joint plate - 86x86
mm



Spring loaded toggle
latch, Standard
(GP22-GP23)



Cylindrical elasto
mount, Steel



Steel spur gear, Steel
20NCD2



Articulated foot with
solid base foot Ø 40,
30000N



Captive C washer, DIN
6371



Pressed steel base
rigid foot, Swivelling
Ø110



Right angle spiro
bevel gearbox, Up to
43Nm



Parallel axis helical
gear, Machined plastic
(delrin)



Hypoid gearbox -
Stainless steel, up to
350 Nm

Complementary products



Wheel, Polyurethane -
Aluminium rim (Free
running)



Stem support for
caster, For swivel
caster with central
hole



Wheel pivoting with
plate, Polyurethane -
Aluminium rim (Free
running)



Fixed castor with
plate, Polyurethane -
Aluminium rim (Free
running)