

Pitch 4.0 to 19.05 mm

Steel

- Compatible with standard HPC sprockets
- Supplied in multiples of either 1 metre, 5 metres (in box) or in chain reel (30 metres or 50 metres) lengths depending on model



Option


- American pitch (ASA) available on request

Accessories

- Roll-Ring® RLR idler (tome 4 p.130 to p.143)



New in chain reel



DISCOUNTS A

No. metres	1+	10+	25+	55+
Discount	List	-5%	-10%	On request

DISCOUNTS B

No. metres	1+	100+
Discount	List	On request

Part number	DIN	Pitch		Roller ØD (mm)	F (mm)	H (mm)	S (mm)	Breaking strength (kN)	Sold in multiples of	Price per metre	
		P (mm)	B (mm)								
In box											
SUA-4	-	4,00	2,70	2,50	6,8	4,1	-	1,8	1 metre	✓ A	252,58 €
SUA-6/M	04-1	6,00	2,80	4,00	7,8	5,0	0,60	3	5 metres	✓ A	12,90 €
SUA-250/M	-	6,35	3,30	3,30	8,0	6,0	-	4	5 metres	✓ A	15,80 €
SBR-8/M	05B-1	8,00	3,00	5,00	8,9	7,1	0,80	5	5 metres	✓ A	12,87 €
SBR-375/M	06B-1	9,52	5,72	6,35	14,1	8,2	1,30	9	5 metres	✓ A	8,24 €
SBR-500/M	08B-1	12,70	7,75	8,51	18,2	11,8	1,60	18	5 metres	✓ A	7,97 €
SBR-625/M	10B-1	15,88	9,65	10,16	20,9	14,7	1,70	22,4	5 metres	✓ A	9,94 €
SBR-750/M	12B-1	19,05	11,68	12,07	24,2	16,0	1,85	29	5 metres	✓ A	12,79 €
In chain reel											
SUA-6/M/T	04-1	6,00	2,80	4,00	7,8	5,0	0,60	3	50 metres	- B	11,30 €
SBR-8/M/T	05B-1	8,00	3,00	5,00	8,9	7,1	0,80	5	50 metres	- B	10,28 €
SBR-375/M/T	06B-1	9,52	5,72	6,35	14,1	8,2	1,30	9	50 metres	- B	6,30 €
SBR-500/M/T	08B-1	12,70	7,75	8,51	18,2	11,8	1,60	18	50 metres	- B	5,99 €
SBR-625/M/T	10B-1	15,88	9,65	10,16	20,9	14,7	1,70	22,4	30 metres	- B	8,19 €
SBR-750/M/T	12B-1	19,05	11,68	12,07	24,2	16,0	1,85	29	30 metres	- B	11,60 €

*Depending on availability - Dimensions in mm

Steel

Pitch 4.0 to 19.05 mm

- Quick fitting
- Connecting link: e.g.: **SUA-4/L**
Offset link: from pitch of 9,52mm,
e.g.: **SBR-375/LC**
- **Not sold individually,**
please contact us for details

Accessories


- Compatible with **SUA** and **SBR** chains
(**tome 4 p.122**)




SUA/L SBR/L



SBR/LC



Connecting link



Offset link

DISCOUNTS

Qty	1+	10+	25+	45+
Disc.	List	-5%	-10%	On request

Part number		DIN	Pitch P (mm)	For chain	Stock*	Stock*	Price each 1 to 9	
Connecting link	Offset link				Connecting link	Offset link	Connecting link	Offset link
SUA-4/L	-	-	4,00	SUA-4	✓	-	12,80 €	-
SUA-6/L	-	04-1	6,00	SUA-6	✓	-	0,92 €	-
SUA-250/L	-	-	6,35	SUA-250	✓	-	1,06 €	-
SBR-8/L	-	05B-1	8,00	SBR-8	✓	-	1,19 €	-
SBR-375/L	SBR-375/LC	06B-1	9,53	SBR-375	✓	✓	0,77 €	1,47 €
SBR-500/L	SBR-500/LC	08B-1	12,70	SBR-500	✓	✓	1,07 €	2,38 €
SBR-625/L	SBR-625/LC	10B-1	15,88	SBR-625	✓	✓	0,77 €	1,81 €
SBR-750/L	SBR-750/LC	12B-1	19,05	SBR-750	✓	✓	1,28 €	2,33 €

* Depending on availability - Dimensions in mm

Single chain supplied by the metre




Pitch 9.52 to 19.05 mm

Stainless steel

- Compatible with standard HPC sprockets
- Supplied in multiples of 5 metres

Accessories

- Chain tensioner section (tome 4 p.130 to p.143)



DISCOUNTS

No metres	1+	10+	25+
Discounts	List	-10%	On request

Part number	DIN	Pitch P (mm)	B (mm)	Roller ØD (mm)	F (mm)	H (mm)	S (mm)	Breaking strength (kN)	Sold in multiples of	Price per metre
SBS-375/M	06B-1	9,52	5,72	6,35	14,0	8,3	1,3	9	5 metres	33,67 €
SBS-500/M	08B-1	12,70	7,75	8,51	18,7	11,8	1,6	18	5 metres	38,88 €
SBS-625/M	10B-1	15,88	9,65	10,16	21,1	14,7	1,70	22,4	5 metres	54,20 €
SBS-750/M	12B-1	19,05	11,68	12,07	24,5	16,1	1,85	29	5 metres	62,14 €

*Depending on availability - Dimensions in mm

Stainless steel


Pitch

9.52 to 19.05 mm

- Quick fitting
- Connecting link: e.g. **SBS-375/L**
- Offset link: e.g. **SBS-375/LC**
- Not sold individually, please contact us for details


Accessories

- Compatible with **SBS stainless steel chains (tome 4 p.124)**



SBS/L

SBS/LC



Connecting link

Offset link

DISCOUNTS

No metres	1+	10+	25+
Discounts	List	-10%	On request

Part number		DIN	Pitch P (mm)	For chain	Stock*	Stock*	Price each 1 to 9	
Connecting link	Offset link				Connecting link	Offset link	Connecting link	Offset link
SBS-375/L	SBS-375/LC	06B-1	9,52	SBS-375	✓	✓	2,84 €	2,87 €
SBS-500/L	SBS-500/LC	08B-1	12,70	SBS-500	✓	✓	2,70 €	4,66 €
SBS-625/L	SBS-625/LC	10B-1	15,88	SBS-625	✓	✓	4,36 €	3,31 €
SBS-750/L	SBS-750/LC	12B-1	19,05	SBS-750	✓	✓	2,24 €	7,08 €

*Depending on availability - Dimensions in mm