
Elingue sangle à 2 boucles


New


SGL1 Gamme violet CMU 1000kg

- ***Elément de levage***
- *Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1*
- *Sangle plate*
- *Largeur 30mm*
- *CMU : charge maximale d'utilisation*











REMISES

Qté	1+	4+	10+	15+
Rem.	Prix	-5%	-10%	Sur demande

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL1-1000	1000	1000	30	7	200	15	
SGL1-1500	1000	1500	30	7	200	15	
SGL1-2000	1000	2000	30	7	200	15	
SGL1-2500	1000	2500	30	7	200	15	
SGL1-3000	1000	3000	30	7	200	15	
SGL1-4000	1000	4000	30	7	200	15	


Dimensions en mm

New


Elingue sangle à 2 boucles


Gamme vert CMU 2000kg — SGL2

- ***Elément de levage***
- *Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1*
- *Sangle plate*
- *Largeur 60mm*
- *CMU : charge maximale d'utilisation*











REMISES

Qté	1+	4+	10+	15+
Rem.	Prix	-5%	-10%	Sur demande

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL2-1000	2000	1000	60	7	300	30	
SGL2-1500	2000	1500	60	7	300	30	
SGL2-2000	2000	2000	60	7	300	30	
SGL2-2500	2000	2500	60	7	300	30	
SGL2-3000	2000	3000	60	7	300	30	
SGL2-4000	2000	4000	60	7	300	30	
SGL2-5000	2000	5000	60	7	300	30	
SGL2-6000	2000	6000	60	7	300	30	
SGL2-8000	2000	8000	60	7	300	30	
SGL2-10000	2000	10000	60	7	300	30	
SGL2-12000	2000	12000	60	7	300	30	


Dimensions en mm

Elingue sangle à 2 boucles


New

SGL3 Gamme jaune CMU 3000kg

- ***Elément de levage***
- *Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1*
- *Sangle plate*
- *Largeur 90mm*
- *CMU : charge maximale d'utilisation*







0°	0°	≤6°	0° à 45°	45° à 60°
F	F x 0,8	F x 2	F x 1,4	F

0° à 45°	0° à 45°	45° à 60°	45° à 60°
F x 1,4	F x 1,12	F	F x 0,8

REMISES

Qté	1+	4+	10+	15+
Rem.	Prix	-5%	-10%	Sur demande

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL3-1000	3000	1000	90	7	350	30	
SGL3-2000	3000	2000	90	7	350	30	
SGL3-3000	3000	3000	90	7	350	30	
SGL3-4000	3000	4000	90	7	350	30	
SGL3-5000	3000	5000	90	7	350	30	
SGL3-6000	3000	6000	90	7	350	30	
SGL3-8000	3000	8000	90	7	350	30	
SGL3-10000	3000	10000	90	7	350	30	
SGL3-12000	3000	12000	90	7	350	30	


Dimensions en mm

New


Elingue sangle à 2 boucles


Gamme gris CMU 4000kg — SGL4

- ***Elément de levage***
- *Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1*
- *Sangle plate*
- *Largeur 120mm*
- *CMU : charge maximale d'utilisation*











REMISES

Qté	1+	4+	10+	15+
Rem.	Prix	-5%	-10%	Sur demande

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL4-1000	4000	1000	120	7	425	40	
SGL4-1500	4000	1500	120	7	425	40	
SGL4-2000	4000	2000	120	7	425	40	
SGL4-2500	4000	2500	120	7	425	40	
SGL4-3000	4000	3000	120	7	425	40	
SGL4-4000	4000	4000	120	7	425	40	
SGL4-5000	4000	5000	120	7	425	40	
SGL4-6000	4000	6000	120	7	425	40	
SGL4-8000	4000	8000	120	7	425	40	
SGL4-10000	4000	10000	120	7	425	40	
SGL4-12000	4000	12000	120	7	425	40	


Dimensions en mm

Elingue sangle à 2 boucles


New


SGL5 Gamme rouge CMU 5000kg

- ***Elément de levage***
- *Sangles polyester haute qualité suivant norme Européenne UNI EN 1492-1*
- *Sangle plate*
- *Largeur 150mm*
- *CMU : charge maximale d'utilisation*











REMISES

Qté	1+	4+	10+	15+
Rem.	Prix	-5%	-10%	Sur demande

Références	Fmax (kg)	Longueur L	W	E	L1	W2	Prix Uni. 1 à 3
SGL5-1000	5000	1000	150	7	500	50	
SGL5-1500	5000	1500	150	7	500	50	
SGL5-2000	5000	2000	150	7	500	50	
SGL5-2500	5000	2500	150	7	500	50	
SGL5-3000	5000	3000	150	7	500	50	
SGL5-4000	5000	4000	150	7	500	50	

Dimensions en mm


Our other products



Idler for slat top chain, Ranges 880 and 881



Internal gear, Machined plastic (delrin)



Flanged sintered ferrous bush, Self-lubricating FP20 ferrous alloy M...



Knurled knob - female, Knurled - blind



Parallel axis helical gear, Steel 20NCD2




Utilitak® V rail, V rail



Ballscrew bearing unit, Support



Telescopic drawer with damper,



Internal gear, Machined plastic



Knurled knob - male, Knurled



Surface mounting plate, Surface



Steel Clamping collar, Steel

Complementary products



Eye bolt high resistance, alloy steel



Female eye bolt high resistance, alloy steel



Female eye bolt high resistance, strenght alloy steel



Master link assembly high resistance, alloy steel