
Stainless steel bevel gear

Ratio 1:1

Stainless steel 304L

- ***Module 0.8 to 2.5***
- *Pressure angle 20°*
- *Teeth Gleason*
- *Material:*
  stainless steel 304L
- *Two gears must be ordered to make a pair*





TORQUE AND POWER INDICATION	For 20 teeth at 1000 rpm					
	2.5 MOD	2.0 MOD	1.5 MOD	1.25 MOD	1.0 MOD	0.8 MOD
Torque (Nm)	4.30	2.20	0.94	0.71	0.57	0.14
Power (kW)	0.455	0.231	0.097	0.08	0.03	0.015

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	Teeth Z	Module	ØP	E	ØD	ØA	ØM	F	G	H	ØR	T	Price each 1 to 5
SSB0.8-16	16		12,80	20	13,93	6	10	16,00	12,21	3,00	M3	7,00	44,47 €
SSB0.8-25	25	**0,8**	20,00	20	21,13	6	16	13,35	8,00	4,24	M3	5,00	48,27 €
SSB0.8-30	30		24,00	20	25,13	6	20	11,96	6,00	5,09	M3	4,00	52,17 €
SSB1-20	20	**1**	20,00	25	21,41	8	18	18,45	14,00	4,24	M4	8,00	53,13 €
SSB1-30	30		30,00	25	31,41	8	26	14,95	8,00	6,35	M4	5,00	60,39 €
SSB1.25-20	20	**1,25**	25,00	23	26,70	8	22	15,27	9,00	6,00	M4	3,50	55,81 €
SSB1.25-30	30		37,50	36	39,30	10	30	23,47	13,50	8,00	M4	5,00	63,23 €
SSB1.5-20	20	**1,5**	30,00	35	32,12	10	26	25,17	18,00	6,35	M4	10,00	57,62 €
SSB1.5-30	30		45,00	35	47,12	10	38	19,92	9,00	9,50	M4	5,00	70,91 €
SSB2-20	20	**2**	40,00	42	43,00	12	34	29,00	19,00	8,50	M5	10,00	67,40 €
SSB2-30	30		60,00	42	63,00	12	50	21,87	7,00	12,70	M5	4,00	84,44 €
SSB2.5-16	16	**2,5**	40,00	50	43,50	15	35	36,80	27,50	8,00	M5	15,00	68,91 €
SSB2.5-25	25		62,50	50	66,00	15	55	30,50	15,00	15,00	M5	8,00	97,78 €

Dimensions in mm

Our other products



BMF

Knurled knob - female, Knurled - blind




RAGFLOW

Floway2® roller track, Roller track



BH02

Single housed bearing assembly, Bearing secured with circlips



PMC150_M16

Anti-vibration machine mount, Square base plate



ZG3

Plastic spur gear, Machined plastic (delrin)



PGMSS

Stainless steel push/pull handle, Stainless steel



ACLRP__

Wheel for aluminium profile, Integrated bearing



MHXred

Reducing sleeve male/female, Hexagonal - stainless steel



H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2



CHM50

Worm and wheel gear reducer, up to 107 Nm



UCP_SS

Stainless steel pillow block bearing, Stainless steel



RJUM05


Drylin R® linear bearing housing, Closed - Long

Complementary products



MEB

Moulded plastic bevel gear (nylon), 1:1



B

Steel bevel gear, 1:1